

Part Number : 2244511112
Product Description : Pre-Crimped Lead Stac64 Female-to-Stac64 Female, Tin (Sn) Plating, 150.00mm Length, 0.75mm^2 Wire, Black
Series Number : 224451
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2244511112_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224451
Description	Pre-Crimped Lead Stac64 Female-to-Stac64 Female, Tin (Sn) Plating, 150.00mm Length, 0.75mm^2 Wire, Black
Application	Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Stac64 Crimp Terminals
Product Name	Stac64
UPC	196823398186

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	14V DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.847/g
Number of Rows	1
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression

Downloaded from Arrow.com.

Wire/Cable Type	FLR2X-A
Wire Size mm^2	0.75

Downloaded from Arrow.com.