







NOTE:

1. Housing : PC UL94V-0
2. Contact : Phosphor Bronze with Tin plating
- 3 Wire : cable sizes :
Solid copper wires up to 0.4mm - 0.8mm in diameter.
Insulation :
PE or PVC insulated wire (100% PE/foam skin, filled/unfilled)
up to 1.4mm in diameter
4. Contact resistance : 10 Milliohms Max.
5. Voltage Rating : 250 VDC
6. Operating Temperature : -20°C to +80°C and Humidity up to 95%
7. Insulation Resistance : 500 VDC, voltage applied 5000 Megohms Min.
- 8 Dielectric Strength : AC 2000 Vrms



PART NUMBER(FOR AA): 15815GJ

PART NUMBER(FOR FRE): E48P0-90031A

REVISION RECORD			
REV	ECO	DESCRIPTION	DRFT
1		Design change	09/30/03

UN (INCH)	DATE 3/28/03	FULL RISE ELECTRONIC CO., LTD	
TOLERANCES EXCEPT AS NOTED	DATE 2003/06/17		
MM	DATE	TITLE IDC TERMINAL BLOCK 8P 15815GJ (BOTTOM CLOSURE)	
±0.20	DATE 2003/06/17		
±0.15		DRAWING NO. GE483119	
±0.075			
ANGLES ±	QTY :	/PART NO. SEE NOTE	
THIRD ANGLE PROJECTION	FINISH :		
	SCALE	DO NOT SCALE DRAWING	

SIZE A3
REV 1/11/03

SHEET X OF Y