

**SRQB 3/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |                                                                                                                                     |
|------------|-------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Cross-connector (terminal), when screwed in, black, 41 A, Number of poles: 2, Pitch in mm (P): 9.00, Insulated: Yes, Width: 14.1 mm |
| Order No.  | <a href="#">2615190000</a>                                                                                                          |
| Type       | SRQB 3/2                                                                                                                            |
| GTIN (EAN) | 4050118653694                                                                                                                       |
| Qty.       | 100 items                                                                                                                           |

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 2.8 mm  | Depth (inches)  | 0.1102 inch |
| Height     | 23 mm   | Height (inches) | 0.9055 inch |
| Width      | 14.1 mm | Width (inches)  | 0.5551 inch |
| Net weight | 1.79 g  |                 |             |

### Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                           |     |        |       |
|---------------------------|-----|--------|-------|
| Basic material            | PA  | Colour | black |
| UL 94 flammability rating | V-2 |        |       |

### System specifications

|         |                 |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

### Additional technical data

|                  |                 |                          |    |
|------------------|-----------------|--------------------------|----|
| Type of fixing   | when screwed in | Explosion-tested version | No |
| Type of mounting | when screwed in |                          |    |

### Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 9.00 mm |
|-----------------|---------|

### General

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

### Rating data

|               |       |                 |      |
|---------------|-------|-----------------|------|
| Rated voltage | 400 V | Nominal current | 41 A |
|---------------|-------|-----------------|------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |