

80×80×38 mm

San Ace 80 9GA type Low Power Consumption Fan 

General Specifications

- Material Frame: Plastic (Flammability: UL 94V-0), Impeller: Plastic (Flammability: UL 94V-0)
- Expected life See the table below. (L10 life: 90% survival rate for continuous operation in free air at 60°C, rated voltage)
Expected life at 40°C is for reference only.
- Motor protection function Locked rotor burnout protection, Reverse polarity protection
For details, please refer to p. 616.
- Dielectric strength 50/60 Hz, 500 VAC, for 1 minute (between lead wire conductors and frame)
- Insulation resistance 10 MΩ min. at 500 VDC (between lead wire conductors and frame)
- Sound pressure level (SPL) A-weighted sound pressure level (SPL) at 1 m away from the air inlet.
- Storage temperature -30 to +70°C (Non-condensing)
- Lead wire ⊕Red ⊖Black Sensor Yellow Control Brown
- Mass 160 g

Specifications

The models listed below **have ribs and a pulse sensor with PWM control**. For models without ribs, append "1" to the end of model numbers.

Model no.	Rated voltage [V]	Operating voltage range [V]	PWM duty cycle [%]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. airflow [m ³ /min] [CFM]	Max. static pressure [Pa] [inchH ₂ O]	SPL [dB (A)]	Operating temperature [°C]	Expected life [h]
9GA0812P1G61	12	10.8 to 13.2	100	1.2	14.4	10500	2.85 100.6	480 1.93	60	-20 to +70	40000/60°C (70000/40°C)
			0	0.07	0.48	2000	0.51 18.0	28.7 0.11	21		
9GA0812P1S61			100	0.94	11.28	9550	2.6 91.8	480 1.93	59		
			0	0.1	1.2	2900	0.74 26.1	60 0.24	27		
9GA0812P1H61	24	20.4 to 27.6	100	0.6	7.2	8250	2.25 79.4	380 1.53	55		
			0	0.08	0.96	2500	0.64 22.6	45 0.18	24		
9GA0824P1S61			100	0.47	11.28	9550	2.6 91.8	480 1.93	59		
			0	0.06	1.44	2900	0.74 26.1	60 0.24	27		
9GA0824P1H61			100	0.3	7.2	8250	2.25 79.4	380 1.53	55		
			0	0.05	1.2	2500	0.64 22.6	45 0.18	24		
9GA0848P1S61	48	40.8 to 55.2	100	0.25	12	9550	2.6 91.8	480 1.93	59		
			0	0.04	1.92	2900	0.74 26.1	60 0.24	27		


* PWM frequency is 25 kHz. Models without ratings for 0% PWM duty cycle have zero speed at 0%. When control terminal is open, speed is the same as at 100% duty cycle.

Note: Sensor and control options are available for selection. Refer to the table on p. 649 to 650.


Airflow - Static Pressure Characteristics / PWM Duty - Speed Characteristics Example

9GA0812P1G61 With pulse sensor with PWM control

PWM duty cycle



Operating voltage range



PWM duty - Speed characteristics example

