




NOTES:

1. RESISTANCE @ 25°C : 2.252KΩ±1%.
2. BETA VALUE (0/50°C) : 3892K±1%.
3. OPERATING TEMPERATURE RANGE : -40°C TO +135°C.
4. DISSIPATION FACTOR : 1.5mW/°C
5. THERMAL TIME CONSTANT : LESS THAN 3SECONDS IN WATER
- 6.INSULATION RESISTANCE : 10MΩ AT 100 VDC

RESISTANCE VS TEMPERATURE CHARACTERISTICS:

Temp(°C)	R min (KΩ)	R nom (KΩ)	R max (KΩ)		Temp(°C)	R min (KΩ)	R nom (KΩ)	R max (KΩ)
-40	72.560	75.920	79.420		50	0.797	0.813	0.830
-35	52.540	54.790	57.140		55	0.660	0.675	0.690
-30	38.480	40.000	41.580		60	0.551	0.564	0.577
-25	28.470	29.510	30.580		65	0.461	0.473	0.486
-20	21.280	21.990	22.720		70	0.388	0.399	0.410
-15	16.010	16.500	17.000		75	0.329	0.338	0.348
-10	12.160	12.500	12.840		80	0.279	0.288	0.297
-5	9.323	9.554	9.790		85	0.239	0.247	0.255
0	7.207	7.367	7.529		90	0.205	0.212	0.219
5	5.613	5.723	5.835		95	0.177	0.183	0.190
10	4.407	4.482	4.558		100	0.153	0.159	0.165
15	3.487	3.538	3.589		105	0.133	0.138	0.144
20	2.779	2.813	2.847		110	0.116	0.121	0.126
25	2.229	2.252	2.275		115	0.102	0.106	0.110
30	1.793	1.815	1.837		120	0.090	0.093	0.097
35	1.451	1.472	1.493		125	0.079	0.082	0.086
40	1.181	1.201	1.221		130	0.069	0.072	0.076
45	0.968	0.985	1.004		135	0.059	0.062	0.066

[illegible]