

PROTECTION PRODUCTS

Description

RailClamp® TVS arrays are ultra low capacitance ESD protection devices designed to protect high speed data interfaces. This series has been specifically designed to protect sensitive components which are connected to high-speed data and transmission lines from overvoltage caused by ESD (electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

RClamp0524PA has a typical capacitance of only 0.3 pF between I/O pins. ESD characteristics are highlighted by high ESD withstand voltage ($\pm 12\text{kV}$ per IEC 61000-4-2), each device will protect four lines operating at 5 volts.

RClamp0524PA is in a DFN 10-Lead package. The flow-through package design simplifies PCB layout.

Features

- Transient Protection to
 - ♦ IEC 61000-4-2 (ESD) $\pm 17\text{ kV}$ (Air), $\pm 12\text{ kV}$ (Contact)
 - ♦ IEC 61000-4-4 (EFT) 40A (5/50ns)
 - ♦ IEC 61000-4-5 (Lightning) 5A (8/20 μs)
- Protects four High-Speed Data Lines
- Package design optimized for high speed lines
- Working voltage: 5V
- Low clamping voltage
- Low capacitance: 0.3 pF typical (I/O to I/O)
- Solid-State Silicon-Avalanche Technology


Mechanical Characteristics

- Package: DFN 10-Lead
- Pb-free, Halogen Free, RoHS/WEEE Compliant
- Lead Finish: Pb-free
- Marking : Marking Code + Date Code
- Packaging : Tape and Reel

Applications


- HDMI 2.0
- Embedded Display Port (eDP)
- Display Port
- LVDS
- V-by-One

Nominal Dimension



Nominal Dimensions in mm


Functional Schematic



Device Schematic


Pin Identification and Configuration

DFN 2.5 x 1.0 x 0.55mm 10-Lead




Pin	Identification
1, 2, 4 and 5	Input Lines
6, 7, 9 and 10	No Internal Connection
3 and 8	Ground

DFN 2.5 x 1.0 x 0.58mm 10-Lead




Pin	Identification
1, 2, 4 and 5	Input Lines
6, 7, 9 and 10	No Internal Connection
3 and 8	Ground

Pin Configuration (Bottom View)



Circuit Diagram

Pin Configuration (Bottom View)



Circuit Diagram

Note:
This device is available with two package outline drawings. Both are compatible with the recommended land pattern. Semtech reserves the right to ship either POD. Please review dimensions of each to guarantee either will work in your design.

Absolute Maximum Rating

Rating	Symbol	Value	Units
Peak Pulse Current (tp = 8/20μs)	I _{PP}	5	A
ESD per IEC 61000-4-2 (Contact) ⁽¹⁾ ESD per IEC 61000-4-2 (Air) ⁽¹⁾	V _{ESD}	±12 ±17	kV
Operating Temperature	T _{OP}	-55 to +125	°C
Junction Temperature and Storage Temperature	T _J & T _{STG}	-55 to +150	°C

Electrical Characteristics (T=25°C unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Reverse Stand-Off Voltage	V _{RWM}	Any I/O pin to GND			5	V
Reverse Breakdown Voltage	V _{BR}	I _t = 1mA, Any I/O pin to GND	6			V
Reverse Leakage Current	I _R	V _{RWM} = 5V			1	μA
Clamping Voltage	V _C	I _{PP} = 1A, tp = 8/20μs, Any I/O pin to GND			15	V
ESD Clamping Voltage ⁽²⁾	V _C	I _{PP} = 4A, tp = 0.2/100ns (TLP) Any I/O pin to GND		10.8		V
		I _{PP} = 16A, tp = 0.2/100ns (TLP) Any I/O pin to GND		13.0		
Dynamic Resistance ⁽²⁾⁽³⁾	R _{DYN}	tp = 0.2/100ns (TLP)		0.19		Ohms
Junction Capacitance	C _J	V _R = 0V, f = 1MHz Any I/O pin to GND			0.8	pF
		V _R = 0V, f = 1MHz Between I/O pins		0.30	0.40	

Notes:


(1) ESD gun return path connected to Ground Reference Plane (GRP)

(2) Transmission Line Pulse Test (TLP) Settings: tp = 100ns, tr = 0.2ns, I_{TLP} and V_{TLP} averaging window: t1 = 70ns to t2 = 90ns.


(3) Dynamic resistance calculated from I_{TLP} = 4A to I_{TLP} = 16A

Typical Characteristics


Non-Repetitive Peak Pulse Power vs. Pulse Time




Surge Clamping Characteristic ($t_p = 8/20\mu$ s)




ESD Clamping (+8kV Contact per IEC 61000-4-2)




ESD Clamping (-8kV Contact per IEC 61000-4-2)



TLP Characteristic (Positive Pulse)




TLP Characteristic (Negative Pulse)




Typical Characteristics

Capacitance vs. Reverse Voltage



Insertion Loss (Line to GND)



Applications Information

Assembly Guidelines

The small size of this device means that some care must be taken during the mounting process to ensure reliable solder joint. The figure at the right details Semtech's recommended mounting pattern. Recommended assembly guidelines are shown in Table 2. Note that these are only recommendations and should serve only as a starting point for design since there are many factors that affect the assembly process. Exact manufacturing parameters will require some experimentation to get the desired solder application. Semtech's recommended mounting pattern is based on the following design guidelines:

Land Pattern

The recommended land pattern follows IPC standards and is designed for maximum solder coverage. Detailed dimensions are shown elsewhere in this document.

Solder Stencil

Stencil design is one of the key factors which will determine the volume of solder paste which is deposited onto the land pad. The area ratio of the stencil aperture will determine how well the stencil will print. The area ratio takes into account the aperture shape, aperture size, and stencil thickness. The area ratio of a rectangular aperture is given as:

$$\text{Area Ratio} = (L * W) / (2 * (L + W) * T)$$

Where:

L = Aperture Length

W = Aperture Width

T = Stencil Thickness

Semtech recommends a stencil thickness of 0.100mm - 0.125mm for this device. The stencil should be laser cut with electro-polished finish. The stencil should have a positive taper of approximately 5 degrees. Electro polishing and tapering the walls results in reduced surface friction and better paste release. Due to the small aperture size, a solder paste with Type 4 or smaller particles is recommended. Assuming a 125um thick stencil, the aperture dimensions shown will yield an area ratio of 0.72 for the small pads and 1.25 for the large.




Table 2 - Recommended Assembly Guidelines

Assembly Parameter	Recommendation
Solder Stencil Design	Laser Cut, Electro-Polished
Aperture Shape	Rectangular
Solder Stencil Thickness	0.100mm (0.004") - 0.125mm (0.005")
Solder Paste Type	Type 4 size sphere or smaller
Solder Reflow Profile	Per JEDEC J-STD-020
PCB Solder pad Design	Non-Solder Mask Defined
PCB Pad Finish	OSP or NiAu

Applications Information

Layout Guidelines for Optimum ESD Protection

Good circuit board layout is critical not only for signal integrity, but also for effective suppression of ESD induced transients. For optimum ESD protection, the following guidelines are recommended:

- Place the device as close to the connector as possible. This practice restricts ESD coupling into adjacent traces and reduces parasitic inductance.
- The ESD transient return path to ground should be kept as short as possible. Whenever possible, use multiple micro vias connected directly from the device ground pad to the ground plane.
- Avoid running critical signals near board edges.






Figure 4. HDMI 1.4 Application using RClamp0524PA

Outline Drawing - DFN 2.5 x 1.0 x 0.55mm 10-Lead




Outline Drawing - DFN 2.5 x 1.0 x 0.58mm 10-Lead



Note:
This device is available with two package outline drawings. Both are compatible with the recommended land pattern. Semtech reserves the right to ship either POD. Please review dimensions of each to guarantee either will work in your design.

Land Pattern - DFN 2.5 x 1.0mm 10-Lead



DIMENSIONS	
DIM	MILLIMETERS
C	(0.875)
G	0.20
P	0.50
X	0.20
X1	0.40
Y	0.675
Z	1.55


- NOTES:
1. CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).
 2. THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY.
CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR
COMPANY'S MANUFACTURING GUIDELINES ARE MET.

Marking Code

0524P
● YYWW

Notes: Dot indicates pin 1 location

Tape and Reel Specification



Ordering Information

Part Number	Qty per Reel	Reel Size
RClamp0524PATCT	3,000	7"



IMPORTANT NOTICE

Information relating to this product and the application or design described herein is believed to be reliable, however such information is provided as a guide only and Semtech assumes no liability for any errors in this document, or for the application or design described herein. Semtech reserves the right to make changes to the product or this document at any time without notice. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. Semtech warrants performance of its products to the specifications applicable at the time of sale, and all sales are made in accordance with Semtech's standard terms and conditions of sale.

SEMTECH PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS, OR IN NUCLEAR APPLICATIONS IN WHICH THE FAILURE COULD BE REASONABLY EXPECTED TO RESULT IN PERSONAL INJURY, LOSS OF LIFE OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. INCLUSION OF SEMTECH PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE UNDERTAKEN SOLELY AT THE CUSTOMER'S OWN RISK. Should a customer purchase or use Semtech products for any such unauthorized application, the customer shall indemnify and hold Semtech and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs damages and attorney fees which could arise.

The Semtech name and logo are registered trademarks of the Semtech Corporation. All other trademarks and trade names mentioned may be marks and names of Semtech or their respective companies. Semtech reserves the right to make changes to, or discontinue any products described in this document without further notice. Semtech makes no warranty, representation or guarantee, express or implied, regarding the suitability of its products for any particular purpose. All rights reserved.

© Semtech 2021

Contact Information

Semtech Corporation
200 Flynn Road, Camarillo, CA 93012
Phone: (805) 498-2111, Fax: (805) 498-3804
www.semtech.com