

2811116

<https://www.phoenixcontact.com/us/products/2811116>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



MCR voltage measuring transducer, for direct current voltages from 0..(+/-)20 V DC to 0..(+/-)660 V DC, output signal (+/-)10 V/(+/-)20 mA

Your advantages

- Adjustable voltage ranges
- Bidirectional output signals
- 3-way isolation
- ZERO/SPAN adjustment $\pm 20\%$
- Tool-free parameterization of measured values
- Teach-in configuration of the measured value range

Commercial data

Item number	2811116
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C440
Product key	CMMB21
GTIN	4017918125394
Weight per piece (including packing)	157.2 g
Weight per piece (excluding packing)	155.2 g
Customs tariff number	85437090
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Voltage transducer
Configuration	INTERBUS

Insulation characteristics

Overvoltage category	II
Pollution degree	2

System properties

Functionality

Configuration	INTERBUS
---------------	----------

Electrical properties

Alignment span	± 20 %
Alignment zero	± 20 %
Frequency measuring range	40 Hz ... 70 Hz
Limit frequency (3 dB)	40 Hz
Test voltage input/output	1.5 kV (50 Hz, 1 min.)
Step response (10-90%)	12 ms
Maximum temperature coefficient	< 0.015 %/K
Maximum transmission error	< 1 % (of final value)

Supply

Supply voltage range	18.5 V DC ... 30.2 V DC
Max. current consumption	< 50 mA

Input data

Measurement

Description of the input	± 550 V input
Input voltage range	-550 V DC ... 550 V DC
Maximum input voltage	± 660 V DC (ungrounded) ± 100 V DC (to earth)
Input resistance of voltage input	550 kΩ
Impulse form	DC voltage

Measurement

Description of the input	± 370 V input
--------------------------	---------------

MCR-VDC-UI-B-DC - Voltage measuring transducers



2811116

<https://www.phoenixcontact.com/us/products/2811116>

Input voltage range	-370 V DC ... 370 V DC
Input resistance of voltage input	370 k Ω

Measurement

Description of the input	± 250 V input
Input voltage range	-250 V DC ... 250 V DC
Input resistance of voltage input	250 k Ω

Measurement

Description of the input	± 170 V input
Input voltage range	-170 V DC ... 170 V DC
Input resistance of voltage input	170 k Ω

Measurement

Description of the input	± 120 V input
Input voltage range	-120 V DC ... 120 V DC
Input resistance of voltage input	120 k Ω

Measurement

Description of the input	± 80 V input
Input voltage range	-80 V DC ... 80 V DC
Input resistance of voltage input	80 k Ω

Measurement

Description of the input	± 54 V input
Input voltage range	-54 V DC ... 54 V DC
Input resistance of voltage input	54 k Ω

Measurement

Description of the input	± 36 V input
Input voltage range	-36 V DC ... 36 V DC
Input resistance of voltage input	36 k Ω

Measurement

Description of the input	± 24 V input
Input voltage range	-24 V DC ... 24 V DC
Input resistance of voltage input	24 k Ω

Output data

Signal: Voltage output

Voltage output signal	-10 V ... 10 V
Max. voltage output signal	± 15 V
Load/output load voltage output	> 10 k Ω
Ripple	< 50 mV _{PP}

Signal: Current output

Current output signal	-20 mA ... 20 mA
-----------------------	------------------

MCR-VDC-UI-B-DC - Voltage measuring transducers



2811116


<https://www.phoenixcontact.com/us/products/2811116>

Max. current output signal	$\pm 30 \text{ mA}$
Load/output load current output	$< 500 \Omega$
Ripple	$< 50 \text{ mV}_{PP}$

Connection data

Connection method	Pluggable screw connection
Connection technology	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section rigid	$0.2 \text{ mm}^2 \dots 2.5 \text{ mm}^2$
Conductor cross section flexible	$0.2 \text{ mm}^2 \dots 2.5 \text{ mm}^2$
Conductor cross section AWG	24 ... 14

Dimensions

Dimensional drawing	
Width	22.5 mm
Height	99 mm
Depth	114.5 mm

Material specifications

Color	green (RAL 6021)
Housing material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	$-25 \text{ }^{\circ}\text{C} \dots 50 \text{ }^{\circ}\text{C}$
Ambient temperature (storage/transport)	$-40 \text{ }^{\circ}\text{C} \dots 85 \text{ }^{\circ}\text{C}$ (non-condensing)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UL, USA/Canada

Identification	cULus
----------------	-------

EMC data

Electromagnetic compatibility	Conformance with EMC directive
-------------------------------	--------------------------------

MCR-VDC-UI-B-DC - Voltage measuring transducers




2811116

<https://www.phoenixcontact.com/us/products/2811116>

Noise immunity	EN 61000-6-2
Noise emission	
Standards/regulations	EN 61000-6-4

Drawings

Dimensional drawing




MCR-VDC-UI-B-DC - Voltage measuring transducers



2811116


<https://www.phoenixcontact.com/us/products/2811116>

Application drawing



Voltage measurement in case of ungrounded circuits

Circuit diagram



Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com