



1. MATERIALS AND FINISHES:
TNC STR BHD JACK IP 67 - BRASS, NICKEL PLATING

CABLE - RG 178


3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-850-284-XXX AND DATE CODE"



RECOMMENDED MOUNTING HOLE DIMENSIONS



SCALE 0.700



LENGTH TABLE	
PART NUMBER (IMPERIAL)	LENGTH AND TOLERANCE 'L' IN MM (INCHES)
95-850-284-050	50.00 ± 3.81 [1.969 ± 0.150]
95-850-284-100	100.00 ± 3.81 [3.937 ± 0.150]
95-850-284-150	150.00 ± 3.81 [5.906 ± 0.150]
95-850-284-200	200.00 ± 5.08 [7.874 ± 0.200]
95-850-284-250	250.00 ± 5.08 [9.843 ± 0.200]
95-850-284-300	300.00 ± 5.08 [11.811 ± 0.200]

☒ FREQUENCY: DC - 6 GHz	☒ CONTINUITY
☐ VSWR: ____ MAX.	☒ HI-POT: 200 VRMS
☐ INS. LOSS: ____ dB MAX.	☐ OTHER:

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE METRIC (INCHES) AND TOLERANCES ARE:

<0.5mm = ±0.05mm	[<0.020 = ±0.002]
>0.5 - 6mm = ±0.1mm	[>0.020 - 0.236 = ±0.004]
>6.00 - 30mm = ±0.2mm	[>0.236 - 1.181 = ±0.008]
>30.00 - 120mm = ±0.3mm	[>1.181 - 4.725 = ±0.012]

MATERIAL

SEE NOTES

ENGR.1
DINESH A

ENGR.2

DATE	29-SEP-21
------	-----------

TITLE

TNC STR BHD JACK IP 67 TO
AMC RA PLUG
USING RG 178 CABLE
VARIOUS LENGTH

SHEET NO. 2 OF 2

SCALE: 2.8:1.0

Amphenol RF

SIZE B	DRAWING NO.	95-850-284-XXX
	ITEM NO.	95-850-284-XXX
	PART NO.	95-850-284-XXX

REV
A

THIRD ANGLE PROJ.

REFERENCE

EAR#
10936

 ANGLES = $\pm 1^\circ$

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY