





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SMALL PRECISION LIMIT SWITCH

CATALOG LISTING
914CE27-0




- NOTES
1 - ZINC HOUSING FINISHED WITH GRAY PAINT
2 - SWITCH MOUNTS THRU A Ø.413 HOLE
3 - .165 MAX PANEL THICKNESS

ANSI Y14.5-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS		ELECTRICAL DATA		SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE 2 LBS 10 1/2 OZ MAX		CONTACT ARRANGEMENT S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE — — — — 1.0 LB MIN		5A 1/10HP 125 OR <u>250</u> VAC  				
DIFFERENTIAL TRAVEL — — — .004 MAX						
OVERTRAVEL — — — — — .118 MIN						
				ONE PLACE (.0)	± .030	
				TWO PLACE (.00)	± .015	
				THREE PLACE (.000)	± .005	
				ANGLES	±	
				WEIGHT		



914CE27-0

M

DRAWING NUMBER

1

ISSUE

REPLACES

RELEASE NO. PR-19359

CHECK

REVISIONS

CHECK

CHECK

14 JUN 91

TSM

DDM/CAD

DRAWN