



Part Number : [878910304](#)
Product Description : KK 254 PCB Header, Through Hole, Breakaway, Vertical, 3 Circuits, 0.38µm Gold (Au) Selective Plating, Tray Packaging, Lead-Free
Series Number : 87891
Status : Active
Product Category : PCB Headers and Receptacles

Documents & Resources

Drawings
[878910304_sd.pdf](#)
[PK-89990-487-001.pdf](#)
[PK-89990-489-001.pdf](#)
[PK-89990-934-001.pdf](#)

Specifications
[PS-87920-019-001.pdf](#)
[879200000-TS-000.pdf](#)
[879200001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	87891
Description	KK 254 PCB Header, Through Hole, Breakaway, Vertical, 3 Circuits, 0.38µm Gold (Au) Selective Plating, Tray Packaging, Lead-Free
Application	Board-to-Board, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	KK 254
UPC	800756741215

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Physical

Breakaway	Yes
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0

Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	5.84mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.161/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	2.97mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	1.905µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 PC Board Connector	<u>4455</u>
SL Single Row Female Insulation Displacement Connector Assemblies	<u>70400</u>
C-Grid III Vertical Single Row PC Board Connectors	<u>90147</u>
C-Grid III Right-Angle Single Row PC Board Connectors	<u>90148</u>

This document was generated on Mar 12, 2025