


VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR HEREWITH IS NOT TO BE REPRODUCED, USED, OR DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT PERMISSION OF VICOR CORP.



REV.	DESCRIPTION	DATE	APPROVED
03	REVSD & REDWN PER E950112 DPK	4/5/95	RCM
4	REVISED PER ECO Request E080622 REJH	03/28/08	EF

ELECTRICAL CHARACTERISTICS

RATED VOLTAGE:	250 VAC, 50/60 Hz
CAPACITANCE TOLERANCE:	± 10%
DISSIPATION FACTOR:	< 1% MEASURED AT 1 KHZ
MAXIMUN PULSE RISE TIME:	ACCORDING TO VDE 0565 PART 1 du/dt 100V / uSEC
DIELECTRIC:	POLYESTER-FILM
TEST VOLTAGE:	(ELECTRODE/ELECTRODE) 1075 V-, 2 SEC. (SELF HEALINGS ARE ALLOWED TO OCCUR)
INSULATION RESISTANCE:	FOR C ≤ .33uF 15000 MEGOHM MINIMUM VALUE
COATING:	PLASTIC CAN, EPOXY RESIN SEALED, FLAME RETARDANT



- NOTES:
1. APPROVALS INCLUDE VDE, SEV, DEMKO, SEMKO, NEMKO, SETI, UL, IMQ, OVE.
 2. LEADS ARE TINNED COPPER WIRE.
 3. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± 1/64 .XX ± .01 ± 1° .XXX ± .005			APPROVALS		DATE					
			DRAWN: <i>D.P. KELLY</i>		4/95					
THIRD ANGLE PROJECTION 							CAP, FLM, AXIAL, 1uF, ±10%/250V			
DO NOT SCALE DRAWING							SIZE	FSCM NO.	DWG. NO.	REV.
							B	67131	02573	4
							SCALE FULL		SHEET 1 OF 1	