

MOSFET - Power, Single P-Channel -40 V, 9.5 mΩ, -77 A NVMFS9D6P04M8L

Features

- Small Footprint for Compact Design
- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- NVMFWS9D6P04M8L – Wettable Flanks Product
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V _{DSS}	-40	V
Gate-to-Source Voltage		V _{GS}	±20	V
Continuous Drain Current R _{θJC} (Notes 1, 2, 4)	Steady State	T _C = 25°C	I _D	A
		T _C = 100°C	-54.4	
Power Dissipation R _{θJC} (Notes 1, 2)		T _C = 25°C	P _D	W
		T _C = 100°C	75	
Continuous Drain Current R _{θJA} (Notes 1, 3, 4)	Steady State	T _A = 25°C	I _D	A
		T _A = 100°C	-17.1	
Power Dissipation R _{θJA} (Notes 1, 3)		T _A = 25°C	P _D	W
		T _A = 100°C	3.7	
Pulsed Drain Current	T _A = 25°C, t _p = 10 µs	I _{DM}	450	A
Operating Junction and Storage Temperature Range		T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)		I _S	-62	A
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = -8.5 A)		E _{AS}	259	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		T _L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


THERMAL RESISTANCE MAXIMUM RATINGS (Note 1)

Parameter	Symbol	Value	Unit
Junction-to-Case – Steady State (Drain) (Notes 1, 2, 4)	R _{θJC}	2	°C/W
Junction-to-Ambient – Steady State (Note 3)	R _{θJA}	40.7	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Assumes heat-sink sufficiently large to maintain constant case temperature independent of device power.
3. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
4. Continuous DC current rating. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

V _{(BR)DSS}	R _{DS(on)} MAX	I _D MAX
-40 V	9.5 mΩ @ -10 V	-77 A
	13.8 mΩ @ -4.5 V	

P-Channel MOSFET



MARKING DIAGRAM



XXXXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 5 of this data sheet.

NVMFS9D6P04M8L

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
-----------	--------	----------------	-----	-----	-----	------

OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0 \text{ V}$, $I_D = -250 \mu\text{A}$	-40			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(\text{BR})\text{DSS}/T_J}$			21		$\text{mV}/^\circ\text{C}$
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{GS}} = 0 \text{ V}$, $V_{\text{DS}} = -40 \text{ V}$	$T_J = 25^\circ\text{C}$		-1.0	μA
			$T_J = 125^\circ\text{C}$		-1000	
Gate-to-Source Leakage Current	I_{GSS}	$V_{\text{DS}} = 0 \text{ V}$, $V_{\text{GS}} = \pm 20 \text{ V}$			± 100	nA

ON CHARACTERISTICS (Note 5)

Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{GS}} = V_{\text{DS}}$, $I_D = -580 \mu\text{A}$	-1.0		-2.4	V
Negative Threshold Temperature Coefficient	$V_{\text{GS}(\text{TH})/T_J}$			-5.1		$\text{mV}/^\circ\text{C}$
Drain-to-Source On Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = -10 \text{ V}$, $I_D = -20 \text{ A}$		7.15	9.5	$\text{m}\Omega$
		$V_{\text{GS}} = -4.5 \text{ V}$, $I_D = -10 \text{ A}$		10.4	13.8	
Forward Transconductance	g_{FS}	$V_{\text{DS}} = -1.5 \text{ V}$, $I_D = -15 \text{ A}$		36		S

CHARGES AND CAPACITANCES

Input Capacitance	C_{iss}	$V_{\text{GS}} = 0 \text{ V}$, $f = 1.0 \text{ MHz}$, $V_{\text{DS}} = -20 \text{ V}$		2002		pF
Output Capacitance	C_{oss}			935		
Reverse Transfer Capacitance	C_{rss}			43		
Total Gate Charge	$Q_{\text{G}(\text{TOT})}$	$V_{\text{DS}} = -20 \text{ V}$, $I_D = -20 \text{ A}$	$V_{\text{GS}} = -4.5 \text{ V}$	15.04		nC
			$V_{\text{GS}} = -10 \text{ V}$	14.47		
Threshold Gate Charge	$Q_{\text{G}(\text{TH})}$	$V_{\text{GS}} = -10 \text{ V}$, $V_{\text{DS}} = -20 \text{ V}$, $I_D = -20 \text{ A}$		4.27		nC
Gate-to-Source Charge	Q_{GS}			11.94		
Gate-to-Drain Charge	Q_{GD}			12.83		
Plateau Voltage	V_{GP}			3.63		V

SWITCHING CHARACTERISTICS, $V_{\text{GS}} = -4.5 \text{ V}$ (Note 6)

Turn-On Delay Time	$t_{\text{d}(\text{on})}$	$V_{\text{GS}} = -4.5 \text{ V}$, $V_{\text{DS}} = -20 \text{ V}$, $I_D = -20 \text{ A}$, $R_G = 2.5 \Omega$		13.1		ns
Rise Time	t_r			103		
Turn-Off Delay Time	$t_{\text{d}(\text{off})}$			83.3		
Fall Time	t_f			63.0		

DRAIN-SOURCE DIODE CHARACTERISTICS

Forward Diode Voltage	V_{SD}	$V_{\text{GS}} = 0 \text{ V}$, $I_S = -20 \text{ A}$	$T_J = 25^\circ\text{C}$		-0.86	-1.25	V
			$T_J = 125^\circ\text{C}$		-0.74		
Reverse Recovery Time	t_{RR}	$V_{\text{GS}} = 0 \text{ V}$, $dI_S/dt = 100 \text{ A}/\mu\text{s}$, $I_S = -20 \text{ A}$			54.6		ns
Charge Time	t_a				34.9		
Discharge Time	t_b				19.7		
Reverse Recovery Charge	Q_{RR}				97.9		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: Pulse Width $\leq 300 \mu\text{s}$, Duty Cycle $\leq 2\%$.

6. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature











Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS




TYPICAL CHARACTERISTICS**Figure 13. Thermal Characteristics****DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping [†]
NVMFS9D6P04M8LT1G	V9D6PL	DFNW5 (Pb-Free)	1500 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS


DFN5 5x6, 1.27P
(SO-8FL)
CASE 488AA
ISSUE N

NOTES:
 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
 2. CONTROLLING DIMENSION: MILLIMETER.
 3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.00	---	0.05
b	0.33	0.41	0.51
c	0.23	0.28	0.33
D	5.00	5.15	5.30
D1	4.70	4.90	5.10
D2	3.80	4.00	4.20
E	6.00	6.15	6.30
E1	5.70	5.90	6.10
E2	3.45	3.65	3.85
e	1.27 BSC	---	---
G	0.51	0.575	0.71
K	1.20	1.35	1.50
L	0.51	0.575	0.71
L1	0.125 REF	---	---
M	3.00	3.40	3.80
θ	0 °	---	12 °

STYLE 1:
 PIN 1. SOURCE
 2. SOURCE
 3. SOURCE
 4. GATE
 5. DRAIN

RECOMMENDED SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the [onsemi](#) Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales