2141116-1 ✔ ACTIVE

MCON | MCON 1.2mm

TE Internal #: 2141116-1

Tab Terminal, 20 – 18 AWG, .5 – .75 mm² Wire, 1.2 mm [.047 in] Tab Width, Tin (Sn), Sealable, .63 mm [.024 in] Tab Thickness, MCON 1.2 mm

View on TE.com >

Automotive Parts > Automotive Terminals



Terminal Type: **Tab**

Wire Size: **20 – 18 AWG**

Mating Tab Width: **1.2 mm [.047 in]**

Interface Plating: **Tin (Sn)**

Features

Product Type Features

Receptacle Style	180°
Primary Locking Feature	Clean Body
Sealable	Yes

Body Features

Terminal Seal Type	Single Wire Seal (SWS)

Contact Features

Crimp Type	F-Crimp
Contact Size	1.2mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Terminal Type	Tab
Mating Tab Width	1.2 mm[.047 in]
Interface Plating	Tin (Sn)
Mating Tab Thickness	.63 mm[.024 in]

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Downloaded from Arrow.com.

Compatible Insulation Diameter Range	1.4 – 1.9 mm[.055 – .075 in]
Wire Size	20 – 18 AWG
Wire Size Search	.5 mm², .6 mm², .75 mm²
Tab Length	25.6 mm[1 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Conforms to Automation Guideline	Yes, DIN 72036 Automation of Wiring Harness Production, Version June 2024, Yes, KOMAX Guideline for automatic component insertion for electrical connections, Version 5.0 (March 2018)

Industry Standards

Compatible With Agency/Standards Products	DIN 72036

Packaging Features

Packaging Method	Reel
Packaging Quantity	6000

Other

Terminal Transmits	0 – 24 A (Low Power)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC

Downloaded from Arrow.com.

	Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1418844-1
MCON 1.2 CB REC SWS SN




TE Part # 967067-2
MQS EINZELLEITDICHT




TE Part # 2151477-1
OCEAN_2.0_APPLICATOR-S-055F125F-RSM



TE Part # 1670146-1
MCON 1.2 CB REC SWS SN




TE Part # 967067-1
MQS SGL WIRE SEAL



TE Part # 7-2151477-7
OCEAN_2.0_SPARE_PART_KIT-055F125F



TE Part # 2327042-3
2POS,MCON 1.2,TAB HSG ASSY,SLD, COD C



TE Part # CAT-N14-RC4812
48V Ready 1.2mm Sealed Connectors



TE Part # 2327042-2
2POS,MCON 1.2,TAB HSG ASSY,SLD, COD B



TE Part # 2151477-2
OCEAN_2.0_APPLICATOR-S-055F125F-RSA



TE Part # 2327042-1
2POS,MCON 1.2,TAB HSG ASSY,SLD, COD A

Also in the Series | MCON 1.2mm


Downloaded from Arrow.com.



Automotive Connector Caps & Covers (15)




Automotive Housings(354)



Automotive Terminals(73)




Connector Seals & Cavity Plugs(16)



Other Automotive Connector Accessories(12)

Customers Also Bought



TE Part #211882-1
CPC PLUG ASSEMBLY SIZE 11



TE Part #2297907-1
12 WAY IN-LINE REC PLUG ASSY



TE Part #2299450-1
14P TAB HOUSING ASSY



TE Part #2304887-1
16POS,HYBRID,TAB HSG ASSY,SLD, COD 1



TE Part #2446122-1
SWS,MCON 1.2,CVTY DIA,3.95,BLK



TE Part #2471991-1
6POS,MCON 1.2,REC HSG ASSY,SLD, COD A



TE Part #2498891-1
6POS,MCON 1.2,TAB HSG,SLD,COD A



TE Part #2322905-3
REC CONN CVR ASSY,75POS,MQS

TE Part #2434842-1
MCON 1.2,TERMINAL,CB,SWS,SN

TE Part #2435067-2
JPT,TERMINAL,A REC 2.8 CONTACT SRC SN

Documents

Downloaded from Arrow.com.

Product Drawings

MCON 1.2 CB TAB SWS SN

English

MCON 1.2 CB TAB SWS SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2141116-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2141116-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2141116-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

German

Application Specification

English

Application Specification

English

Downloaded from Arrow.com.