

Mounts with round design, self adhesive

RA-Series


These mounts are ideal for use in applications which are difficult to access or for areas where self adhesive is the only possible fixing method and fixing holes would be unacceptable. The round self adhesive mounts can be used without cable ties. Offering process optimization in industries like automotive, bus and truck, construction vehicles or industrial building.

Features and benefits

- One-piece self adhesive mount for quick and easy installation
- Can be used without cable ties offering process optimization
- Designed to hold wires, cables or hoses
- Different sizes for various bundle diameters available
- Two types of adhesive can be offered



Self adhesive one piece fixing mounts RA6 (l) and RB5 (r).



RA3-18 Series
(side view)

RA3-18 Series (plan view)



For more information on the types of adhesive please see page 134.

TYPE	Width (W)	Width (W2)	Length (L)	Height (H)	Bundle Ø max.	Material	Colour	Adhesive	Article-No.
RA3	13.0	5.0	13.0	5.0	3.0	PA66	Natural (NA)	Synthetic rubber T60	151-13018
RA6APT-I	19.0	5.0	19.0	9.0	6.0	PA66	Natural (NA)	mod. Acrylate	151-01635
RA6	19.0	5.0	19.0	9.0	6.0	PA66	Natural (NA)	Synthetic rubber T60	151-13019
RA9	19.0	7.5	19.0	12.5	9.0	PA66	Natural (NA)	Synthetic rubber T60	151-13020
RA13APT-I	25.0	10.0	25.0	16.5	13.0	PA66	Natural (NA)	mod. Acrylate	151-01636
RA13	25.0	10.0	25.0	16.5	13.0	PA66	Natural (NA)	Synthetic rubber T60	151-13021
RA18	28.5	10.0	28.5	23.0	18.0	PA66	Natural (NA)	Synthetic rubber T60	151-13119

All dimensions in mm. Subject to technical changes.

Material Specification Overview

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Aluminium-alloy	AL	-40 °C to +180 °C	Natural (NA)		- Corrosion resistant - Antimagnetic	RoHS
Chloroprene	CR	-20 °C to +80 °C	Black (BK)		- Weather-resistant - High yield strength	RoHS
Ethylene Tetrafluoroethylene (Tefzel®)	E/TFE	-80 °C to +170 °C	Blue (BU)	UL 94 V0	- Resistance to radioactivity - UV-resistant, not moisture sensitive - Good chemical resistance to: acids, bases, oxidizing agents	RoHS
Polyacetal	POM	-40 °C to +90 °C, (+110 °C, 500 h)	Natural (NA)	UL 94 HB	- Limited brittleness sensitivity - Flexible at low temperature - Not moisture sensitive - Robust on impacts	RoHS
Polyamide 11	PA11	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Bio-plastic, derived from vegetable oil - Strong impact resistance at low temperature - Very low moisture absorption - Weather-resistant - Good chemical resistance	HF RoHS
Polyamide 12	PA12	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Good chemical resistance to: acids, bases, oxidizing agents - UV-resistant	HF RoHS
Polyamide 4.6	PA46	-40 °C to +150 °C (5000 h), +195 °C (500 h)	Natural (NA), Grey (GY)	UL 94 V2	- Resistance to high temperatures - Very moisture sensitive - Low smoke sensitiv	HF LFH RoHS
Polyamide 6	PA6	-40 °C to +80 °C	Black (BK)	UL 94 V2	High yield strength	RoHS
Polyamide 6, high impact modified	PA6HIR	-40 °C to +80 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6	PA66	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK), Natural (NA)	UL 94 V2	High yield strength	HF RoHS
Polyamide 6.6, glass-fibre reinforced	PA66GF13, PA66GF15	-40 °C to +105 °C	Black (BK)	UL 94 HB	Good resistance to: lubricants, vehicle fuel, salt water and a lot of solvent	HF RoHS
Polyamide 6.6, heat and UV stabilised	PA66HSW	-40 °C to +105 °C	Black (BK)	UL 94 V2	- High yield strength - Modified elevated max. temperature - UV-resistant	HF RoHS
Polyamide 6.6, heat stabilised	PA66HS	-40 °C to +105 °C	Black (BK), Natural (NA)	UL 94 V2	- High yield strength - Modified elevated max. temperature	HF RoHS
Polyamide 6.6, high impact modified	PA66HIR	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6, high impact modified, heat and UV stabilised	PA66HIRHSW	-40 °C to +110 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature - Modified elevated max. temperature - High yield strength, UV-resistant	RoHS
Polyamide 6.6, high impact modified, heat stabilised	PA66HIRHS	-40 °C to +105 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature - Modified elevated max. temperature	RoHS
Polyamide 6.6, high impact modified, ScanBlack	PA66HIR(S)	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6, UV-resistant	PA66W	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 V2	- High yield strength - UV-resistant	HF RoHS

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Polyamide 6.6, with metal particles	PA66MP	-40 °C to +85 °C, (+105 °C, 500 h)	Blue (BU)	UL 94 HB	- High yield strength - Metal and X-Ray detectable	HF RoHS
Polyamide 6.6, with metal particles	PA66MP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	- High yield strength - Metal and x-ray detectable	HF RoHS
Polyamide 6.6 V0	PA66V0	-40 °C to +85 °C	White (WH)	UL 94 V0	- High yield strength - Low smoke emission	HF LFH RoHS
Polyester	SP	-50 °C to +150 °C	Black (BK)	halogen free	- UV-resistant - Good chemical resistance to: most acids, alkalis and oils	HF LFH RoHS
Polyetheretherketone	PEEK	-55 °C to +240 °C	Beige (BGE)	UL 94 V0	- Resistance to radioactivity - Not moisture sensitive - Good chemical resistance to: acids, bases, oxidizing agents	HF LFH RoHS
Polyethylene	PE	-40 °C to +50 °C	Black (BK), Grey (GY)	UL 94 HB	- Low moisture absorption - Good chemical resistance to: most acids, alcohol and oils	HF RoHS
Polyolefin	PO	-40 °C to +90 °C	Black (BK)	UL 94 V0	Low smoke emissions	HF LFH RoHS
Polypropylene	PP	-40 °C to +115 °C	Black (BK), Natural (NA)	UL 94 HB	- Floats in water - Moderate yield strength - Good chemical resistance to: organic acids	HF RoHS
Polypropylene, Ethylene-Propylene-Dien-Terpolymere-rubber free of Nitrosamine	PP, EPDM	-20 °C to +95 °C	Black (BK)	UL 94 HB	- Good resistance to high temperatures - Good chemical and abrasion resistance	HF RoHS
Polypropylene with metal particles	PPMP	-40 °C to +115 °C	Blue (BU)	UL 94 HB	- Metal and X-Ray detectable - Heat resistant - Moderate yield strength - Good chemical resistance	RoHS
Polypropylene with metal particles	PPMP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	- High yield strength - Metal and x-ray detectable	HF RoHS
Polyvinylchloride	PVC	-10 °C to +70 °C	Black (BK), Natural (NA)	UL 94 V0	- Low moisture absorption - Good chemical resistance to: acids, ethanol and oil	RoHS
Stainless Steel	SS304, SS316	-80 °C to +538 °C	Natural (NA)	non-burning	- Corrosion resistant - Antimagnetic - Weather resistant - Outstanding chemical resistance	HF LFH RoHS
Thermoplastic Polyurethane	TPU	-40 °C to +85 °C	Black (BK)	UL 94 HB	- High elastic - Good chemical resistance to: acids, bases and oxidizing agents	HF RoHS

Tefzel® is a registered trademark of DuPont. General linguistic usage for cable ties made from raw material E/TFE is Tefzel®-Tie. In addition to Tefzel® from DuPont HellermannTyton is also using equivalent E/TFE raw material from other suppliers. *These details are only rough guide values. They should not be regarded as a material specification and are no substitute for a suitability test. Please see our datasheets for further details.

**More colours on request.



Minimum Loop Tensile Strength for Cable Ties (Newton)

HF = Halogenfree

LFH = Limited Fire Hazard

RoHS = Restriction of Hazardous Substances