

5

4

3

2

1

NOTES:

1. MATERIALS AND FINISHES:
MMCX STR PLUG - BRASS, GOLD PLATING
CABLE - RG 174

2. ELECTRICAL:
A. IMPEDANCE: 50 OHM

3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-900-548-XXX AND DATE CODE"

REVISIONS

REV	DESCRIPTION	DATE	ECN	BY
A	RELEASE TO MFG.	09-JUN-21	15736	DSK

SCALE 0.800

LENGTH 'L' SEE TABLE

HEAT SHRINK TUBE
TYP(2)

INTERFACE PER
MMCX PLUG
TYP(2)

25.40±1.27
[1.000±0.050]
TYP(2)

LENGTH TABLE

PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH 'L' IN INCHES [METERS]
95-900-548-006	-	6.00 [0.152]
-	95-900-548M025	9.84 [0.250]
95-900-548-012	-	12.00 [0.305]
95-900-548-018	-	18.00 [0.457]
-	95-900-548M050	19.69 [0.500]
95-900-548-024	-	24.00 [0.610]
-	95-900-548M075	29.53 [0.750]
95-900-548-036	-	36.00 [0.914]
-	95-900-548M100	39.37 [1.000]
95-900-548-048	-	48.00 [1.219]
-	95-900-548M200	78.74 [2.000]
-	95-900-548M300	118.11 [3.000]

TOLERANCE TABLE

LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

☒ FREQUENCY: DC - 1 GHz

☒ CONTINUITY

☐ VSWR: ____ 1 MAX.

☒ HI-POT: 300 VRMS

☐ INS. LOSS: ____ dB MAX.

☐ OTHER

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

THIRD ANGLE PROJ.

REFERENCE

EAR#
10677

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE:
<0.5mm = ±0.05mm [$<0.020 = \pm0.002$]
>0.5 - 6mm = ±0.1mm [$>0.020 - 0.236 = \pm0.004$]
>6.00 - 30mm = ±0.2mm [$>0.236 - 1.181 = \pm0.008$]
>30.00 - 120mm = ±0.3mm [$>1.181 - 4.725 = \pm0.012$]

ANGLES = ±1°

MATERIAL

SEE NOTES

ENGINEER
SASI D

DATE
09-MAY-21

TITLE

MMCX STR PLUG TO
MMCX STR PLUG
USING RG 174 CABLE
VARIOUS LENGTH

SHEET NO. 2 OF 2

SCALE: 2.2:1.0

Amphenol RF

SIZE
B

DRAWING NO. 95-900-548-XXX
ITEM NO. 95-900-548-XXX
PART NO. 95-900-548-XXX

REV
A

5

4

3

2

1

Downloaded from Arrow.com