




Positions	A	B	C	E	F
9	30.81	24.99	16.92	11.08	19.20
15	39.20	33.30	25.25	19.39	27.70
25	53.04	47.04	38.96	33.24	41.10
37	69.40	63.50	55.42	49.86	57.30



50 Positions

REVISIONS


SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	Apr/30/2013	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 100u" min tin over 50u" min nickel
over 50u" min Copper
BODY : Glass-Filled Thermoplastic PBT,UL94V-0
CONTACTS : Copper alloy
Gold flash over 50u" min nickel on mating area.
100u" min tin over 50u" min nickel on solder area.
SCREWLOCK : Brass, Nickel Plated
ELECTRICAL : Voltage rating 250 VAC/Rms 60Hz
Current rating 3A.
Withstanding Voltage >1000 VAC/Rms 60Hz for one minute
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms Max.
MARKING : Amphenol---(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 717 SD X XX P VFM



UNLESS OTHERWISE SPECIFIED			APPROVAL		DATE		
TOLERANCES			DRAWN	Bydly	Apr/30/2013		
U.S.			CHECKED	Visent	Apr/30/2013		
.X	+/-	0.50	CHECKED				
.XX	+/-	0.30					
.XXX	+/-	0.20					
FRACTIONS	+/-						
ANGLES	+/-	5°					
FOR MATERIALS AND FINISHES							
SEE NOTES							
REMOVE SHARP EDGES							
DIMENSIONS			DRAWING FILE :				
U-S	INCHES	ANGLE OF PROJECTION					
METRIC	MM						
							
TITLE							
D-sub,solder cup,G/F							
SIZE DRAWING NO.			REV.				
A4			1				
L717SDXXXVFM							
SCALE			SHEET 1 OF 1				
NONE							