




NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. MATERIALS AND FINISHES (IN MICRO-INCHES)
 - BODY = BRASS (PER QQ-B-626, ALLOY 360, 1/2H OR EQUIVALENT)
 - NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 - CONTACT = BERYLLIUM COPPER (PER QQ-C-530, ALLOY C173, 1/2H OR EQUIVALENT), GOLD PL. 30 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 - INSULATOR = PTFE PER MIL-P-19468; NATURAL
 - LOCK COVER = NYLON 66 WITH 33% GLASS FILLED, PER NYTEX COMPOSITES CO., LTD. GRADE MG-0033N-V0 OR EQUIVALENT (REFER TO TABLE BELOW FOR KEY CODE COLOR)
 - FERRULE = COPPER (PER ASTM B-75 ALLOY C12200 OR EQUIVALENT) NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 - BARREL = BRASS (PER QQ-B-626, ALLOY 360, 1/2H OR EQUIVALENT) NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM (NOMINAL)
 - B. FREQUENCY RANGE: DC - 6 GHz (OPTIMIZED FOR DC-4GHz)
 - C. VSWR (RETURN LOSS): 1.4 (-15.6 dB), MAX. (DC-2GHz) (MATED PAIR) 1.5 (-13.9 dB), MAX. (2-3GHz)
 - D. DIELECTRIC WITHSTANDING VOLTAGE: 800 VRMS, MIN.
3. MECHANICAL:
 - A. DURABILITY: 100 CYCLES MIN.
 - B. TEMPERATURE RANGE: -40° C TO 100° C
4. PACKAGING:
 - A. QUANTITY: TRAY PACK
 - B. MARKING: TRAY TO BE MARKED "AMPHENOL FAI-NXSJ-C01-0, AND DATE CODE"
5. CRIMPED FERRULE
HEX CRIMP SIZE .128"
6. CRIMPED CONTACT PIN AFM8
ADJUST TO 4
POSITIONER K727



RECOMMENDED
CABLE STRIPPING DIM'S



TABLE

CODING	DRAWING NO.	PART NO.	COLOR	RAL NO.
A	FK6121AW-007-NT30G-50	FAI-NASJ-C01-0	JET BLACK	9005
B	FK6121BW-007-NT30G-50	FAI-NBSJ-C01-0	CREAM	9001
C	FK6121CW-007-NT30G-50	FAI-NCSJ-C01-0	SIGNAL BLUE	5005
D	FK6121DW-007-NT30G-50	FAI-NDSJ-C01-0	CLARET VIOLET	4004
E	FK6121EW-007-NT30G-50	FAI-NESJ-C01-0	LEAF GREEN	6002
F	FK6121FW-007-NT30G-50	FAI-NFSJ-C01-0	NUT BROWN	8011
G	FK6121GW-007-NT30G-50	FAI-NGSJ-C01-0	BLUE GREY	7031
H	FK6121HW-007-NT30G-50	FAI-NHSJ-C01-0	HEATHER VIOLET	4003
I	FK6121IW-007-NT30G-50	FAI-NISJ-C01-0	BEIGE	1001
K	FK6121KW-007-NT30G-50	FAI-NKSJ-C01-0	CURRY	1027
L	FK6121LW-007-NT30G-50	FAI-NLSJ-C01-0	CARMINE RED	3002
M	FK6121MW-007-NT30G-50	FAI-NMSJ-C01-0	PASTEL ORANGE	2003
N	FK6121NW-007-NT30G-50	FAI-NNSJ-C01-0	PASTEL GREEN	6019
Z	FK6121ZW-007-NT30G-50	FAI-NZSJ-C01-0	WATER BLUE	5021

CONFIGURATION CONTROL:
NO CHANGES PERMITTED TO DRAWING WITHOUT
PPAP QUALIFIED CUSTOMER APPROVAL

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp., the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

DRAWN
E.TANG
ENGINEER
ANGELA

DATE
28-Sep-07

DATE
28-Sep-07

REFERENCE

APPROVED
ANGELA

DATE
28-Sep-07

FINISH

1:\FAKRA\FK6121XX-007-NT30G-50

TITLE
FAKRA SMB CRIMP JACK
(FOR RG-174/U, 188/U,
316/U CABLE)

SCALE: 2.0:1.0 SHEET 2 OF 2

DWG SIZE
B

CODE ID
74868

REV
G

Amphenol RF

Danbury CT USA, Tainan, Taiwan, Shenzhen, China
www.amphenolrf.com

DRAWING NO. FK6121XX-007-NT30G-50

ITEM NO. FK6121AAX36NC5F

PART NO. FAI-NXSJ-C01-0