


DETAIL Z
SCALE 8:1

NOTES:

1. MATERIAL: HOUSING: NYLON, UL94V-1, COLOR: BLACK
PINS: BRASS
2. FINISH: (197) = OVERALL REFLOWED MATTE TIN: 0.00152/.000060 MIN.
OVER 0.00127/.000050 MIN. NICKEL OVERALL.
(208) = SELECT GOLD: 0.00038/.000015 MIN,
SELECT MATTE TIN: 0.00254/.000100 MIN,
BOTH OVER 0.00127/.000050 MIN NICKEL.
(228) = SELECT GOLD: 0.00076/.000030 MIN,
SELECT MATTE TIN: 0.00254/.000100 MIN,
BOTH OVER 0.00127/.000050 MIN NICKEL.
3. PRODUCT SPECIFICATION: PS-171813-0001, PS-171813-0002
4. PACKAGING INFORMATION: SEE CHART
5. SOLDERABILITY: PER SMES-152.
6. PIN PUSH-OUT FORCE: PRIOR TO SOLDERING, A 3 LB. MINIMUM FORCE
IN EITHER DIRECTION
7. PARTS ARE STACKABLE END TO END ON 3.96/.156 CENTERS.
8. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC
SPECIFICATION PS-45499-002.
9. SLOTS ON BACKWALL ARE BETWEEN CIRCUITS. SEE CHART FOR LOCATION.
10. CIRCUIT 1 DESIGNATION IS USED TO DEFINE VOID LOCATION. CIRCUIT 1
MAY OR MAY NOT LINE UP WITH CIRCUIT 1 ON THE MATING HOUSING.
11. FEATURE MAY OR MAY NOT EXTEND ACROSS THE ENTIRE FACE OF THE PART.
SEE DETAIL Z.
12. THE PARTS LISTED ON THIS DRAWING ARE CONSTRUCTED TO MEET THE
REQUIREMENT FOR DIRECT SUPPORT OF UNINSULATED LIVE PARTS
AS DESCRIBED IN UL508C.

FEATURE MAY BE ON EITHER
SIDE OF THE PART

SEE NOTE 11
AND DETAIL Z

11.33±0.51
.446±.020

2.41
.095
REF

-E-

5.11
.201
AT DATUM -D-

GOLD

M ±0.38 TYP
±.015

3.30
.130 REF

Y ±0.25 TYP
±.010

CENTERLINE OF PIN AT TIP
NOT TO VARY FROM CENTERLINE OF
PIN AT DATUM -E- BY MORE THAN
0.20 / .008 IN ANY DIRECTION.

TIN

P
REF.

10.01±0.51
.394±.020

3.96±0.05 TYP
.156±.002
NON-ACCUMULATIVE

1.73±0.05 DIA TYP
.068±.002

PCB LAYOUT: COMPONENT SIDE

CENTERLINE OF PIN AT TIP
NOT TO VARY FROM CENTERLINE OF
PIN AT DATUM -D- BY MORE THAN
0.20 / .008 IN ANY DIRECTION.

SEE DETAIL Z
SEE NOTE 11

OPTIONAL VOIDED CIRCUIT
SEE CHART FOR LOCATIONS

CIRCUIT 1
SEE NOTE 10

SEE NOTE 9

-D-

CIRCUIT SIZE	DIM. A	DIM. B	SLOT LOCATION BETWEEN CIRCUITS
2	7.77 .306	3.96±0.05 .156±.002	NONE
3	11.73 .462	7.92±0.10 .312±.004	NONE
4	15.70 .618	11.89±0.15 .468±.006	NONE
5	19.66 .774	15.85±0.15 .624±.006	NONE
6	23.62 .930	19.81±0.18 .780±.007	3 & 4
7	27.58 1.086	23.77±0.18 .936±.007	4 & 5
8	31.55 1.242	27.74±0.20 1.092±.008	4 & 5
9	35.51 1.398	31.70±0.20 1.248±.008	5 & 6
10	39.47 1.554	35.66±0.23 1.404±.009	5 & 6
11	43.43 1.710	39.62±0.23 1.560±.009	6 & 7
12	47.40 1.866	43.59±0.25 1.716±.010	4 & 5 8 & 9

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION UNITS		SCALE		molex® KK RPC .156 HEADER ASS'Y FRICTION LOCK RIGHT ANGLE W/O PEGS							
						MM/IN		4:1									
= 0	ADD NOTE 12	EC NO: 113073 DRWN: BAPPELDORN CHK'D: JBELL REV APPR: FSMITH	2017/02/03 2017/02/06 2017/02/09		MM	INCH	DRWN BY		DATE								
= 0				4 PLACES	±		±	MKIPPER		2012/09/14							
= 0				3 PLACES	±		± 0.01	CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING					
= 0				2 PLACES	±	0.25	± 0.015	SSOUSEK		2012/09/14							
= 0				1 PLACES	±	0.38	±	APPR BY		DATE		SERIES MATERIAL NUMBER CUSTOMER					
= 0				0 PLACES	±		±	FSMITH		2013/06/11							
= 0				ANGULAR TOL ± 0.5				DRAWING SIZE		THIRD ANGLE PROJECTION		171814 SEE CHART GENERAL MARKET					
= 0				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				C								DOCUMENT NUMBER SD-171814-0001	
= 0				B1		REV						DOC TYPE PSD		DOC PART 000			

OPTIONS	Group	171814-0002/0012	Group	171814-1002/1012	Group	171814-2002/2012
	Plating:	197 – TIN	Plating:	208 – 15 GOLD	Plating:	228 – 30 GOLD
	Mating M	11.33 / .446	Mating M	11.33 / .446	Mating M	11.33 / .446
	Gold Loc G	N/A	Gold Loc G	6.85 / .270	Gold Loc G	6.85 / .270
	Height Y	5.41 / .213	Height Y	5.41 / .213	Height Y	5.41 / .213
	PC Tail P	2.54/ .100	PC Tail P	2.54/ .100	PC Tail P	2.54/ .100
	Tin Loc T	OVERALL	Tin Loc T	5.08 / .200	Tin Loc T	5.08 / .200
	Voided Ckts	NONE	Voided Ckts	NONE	Voided Ckts	NONE
	Pack Per	PK-41792-002 BULK	Pack Per	PK-41792-002 BULK	Pack Per	PK-41792-002 BULK
Ckts	Material No		Material No		Material No	
2	171814-0002		171814-1002		171814-2002	
3	171814-0003		171814-1003		171814-2003	
4	171814-0004		171814-1004		171814-2004	
5	171814-0005		171814-1005		171814-2005	
6	171814-0006		171814-1006		171814-2006	
7	171814-0007		171814-1007		171814-2007	
8	171814-0008		171814-1008		171814-2008	
9	171814-0009		171814-1009		171814-2009	
10	171814-0010		171814-1010		171814-2010	
11	171814-0011		171814-1011		171814-2011	
12	171814-0012		171814-1012		171814-2012	

REV:	<u>ECR/ECN INFORMATION:</u>	<u>TITLE:</u>	<u>SHEET No.</u>
A5	EC No.:	KK RPC 156 HEADER ASSEMBLY FRICTION LOCK RIGHT ANGLE W/O PEGS	- 2 -
	DATE: 11/19/2020		
<u>DOCUMENT NUMBER:</u>	<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>	<u>APPROVED BY:</u>
SD-171814-0001	SS06	YVENKATESWAR	ISHWARG

OPTIONS	Group	171814-0102/0112	Group	171814-1104	Group	
	Plating:	197 – TIN	Plating:	208 – 15 GOLD	Plating:	
	Mating M	11.43 / .450	Mating M	11.43 / .450	Mating M	
	Gold Loc G	N/A	Gold Loc G	6.85 / .270	Gold Loc G	
	Height Y	5.41 / .213	Height Y	5.41 / .213	Height Y	
	PC Tail P	3.96/ .156	PC Tail P	3.96/ .156	PC Tail P	
	Tin Loc T	OVERALL	Tin Loc T	5.08 / .200	Tin Loc T	
	Voided Ckts	NONE	Voided Ckts	NONE	Voided Ckts	
	Pack Per	PK-41792-002 BULK	Pack Per	PK-41792-002 BULK	Pack Per	
Ckts	Material No		Material No		Material No	
2	171814-0102					
3	171814-0103					
4	171814-0104		171814-1104			
5	171814-0105					
6	171814-0106					
7	171814-0107					
8	171814-0108					
9	171814-0109					
10	171814-0110					
11	171814-0111					
12	171814-0112					

REV:	<u>ECR/ECN INFORMATION:</u>	<u>TITLE:</u>	<u>SHEET No.</u>
A5	EC No.:	KK RPC 156 HEADER ASSEMBLY FRICTION LOCK RIGHT ANGLE W/O PEGS	- 3 -
	DATE: 11/19/2020		
<u>DOCUMENT NUMBER:</u>	<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>	<u>APPROVED BY:</u>
SD-171814-0001	SS06	YVENKATESWAR	ISHWARG

OPTIONS	Group	171814-3002/3012	Group	171814-4002/4012	Group	
	Plating:	197 – TIN	Plating:	208 – 15 GOLD	Plating:	
	Mating M	11.33 / .446	Mating M	11.33 / .446	Mating M	
	Gold Loc G	N/A	Gold Loc G	6.85 / .270	Gold Loc G	
	Height Y	5.41 / .213	Height Y	5.41 / .213	Height Y	
	PC Tail P	2.54/ .100	PC Tail P	2.54/ .100	PC Tail P	
	Tin Loc T	OVERALL	Tin Loc T	5.08 / .200	Tin Loc T	
	Voided Ckts	NONE	Voided Ckts	NONE	Voided Ckts	
	Pack Per	PK-171814-0001 TAPE AND REEL	Pack Per	PK-171814-0001 TAPE AND REEL	Pack Per	
Ckts	Material No		Material No		Material No	
2	171814-3002		171814-4002			
3	171814-3003		171814-4003			
4	171814-3004		171814-4004			
5	171814-3005		171814-4005			
6	171814-3006		171814-4006			
7	171814-3007		171814-4007			
8	171814-3008		171814-4008			
9	171814-3009		171814-4009			
10	171814-3010		171814-4010			
11	171814-3011		171814-4011			
12	171814-3012		171814-4012			

REV:	<u>ECR/ECN INFORMATION:</u>	<u>TITLE:</u>	<u>SHEET No.</u>
A5	EC No.:	KK RPC 156 HEADER ASSEMBLY FRICTION LOCK RIGHT ANGLE W/O PEGS	- 4 -
	DATE: 11/19/2020		
<u>DOCUMENT NUMBER:</u>	<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>	<u>APPROVED BY:</u>
SD-171814-0001	SS06	YVENKATESWAR	ISHWARG

OPTIONS	Group	171814-9999	Group	171814-7002/7012	Group	171814-7105
	Plating:	197 – TIN	Plating:	228 – 30 GOLD	Plating:	228 – 30 GOLD
	Mating M	11.43 / .450	Mating M	11.43 / .450	Mating M	11.43 / .450
	Gold Loc G	N/A	Gold Loc G	6.85 / .270	Gold Loc G	6.85 / .270
	Height Y	5.41 / .213	Height Y	5.41 / .213	Height Y	5.41 / .213
	PC Tail P	3.96/ .156	PC Tail P	3.96/ .156	PC Tail P	3.96/ .156
	Tin Loc T	OVERALL	Tin Loc T	5.08 / .200	Tin Loc T	5.08 / .200
	Voided Ckts	3, 5, 7	Voided Ckts	NONE	Voided Ckts	2,4
	Pack Per	PK-41792-002 BULK	Pack Per	PK-41792-002 BULK	Pack Per	PK-41792-002 BULK
Ckts	Material No		Material No		Material No	
2						
3						
4			171814-7004			
5					171814-7105	
6						
7	171814-9999					
8						
9			171814-7009			
10						
11						
12						

REV:	<u>ECR/ECN INFORMATION:</u>	<u>TITLE:</u>	<u>SHEET No.</u>
A5	EC No.:	KK RPC 156 HEADER ASSEMBLY FRICTION LOCK RIGHT ANGLE W/O PEGS	- 5 -
	DATE: 11/19/2020		
<u>DOCUMENT NUMBER:</u>	<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>	<u>APPROVED BY:</u>
SD-171814-0001	SS06	YVENKATESWAR	ISHWARG

OPTIONS	Group	171814-9998
	Plating:	197 – TIN
	Mating M	11.33 / .446
	Gold Loc G	N/A
	Height Y	5.41 / .213
	PC Tail P	2.54/ .100
	Tin Loc T	OVERALL
	Voided Ckts	2
	Pack Per	PK-41792-002 BULK
Ckts	Material No	
2		
3	171814-9998	
4		
5		
6		
7		
8		
9		
10		
11		
12		

REV: A5	<u>ECR/ECN INFORMATION:</u>	<u>TITLE:</u> KK RPC 156 HEADER ASSEMBLY FRICTION LOCK RIGHT ANGLE W/O PEGS			<u>SHEET No.</u> - 6 -
	<u>EC No.:</u>				
	<u>DATE:</u> 11/19/2020				
<u>DOCUMENT NUMBER:</u> SD-171814-0001		<u>CREATED / REVISED BY:</u> SS06	<u>CHECKED BY:</u> YVENKATESWAR	<u>APPROVED BY:</u> ISHWARG	