

HONEYWELL PART NUMBER
91SX49
PRODUCT CODE VDQ9131

REV	DOCUMENT	CHANGED BY	CHECK
3	0038450	PK 03JUN08	ASD


B

A

A

B

A



NOTES
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREW
OF Ø.087 MAX ON .188±.002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.	PR-21572
REPLACES	X96327-SX

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	SPK	04MAR08	Honeywell			
OPERATING FORCE ----- 5 OZ MAX		CONTACT ARRANGEMENT SPDT							CHECK	RJ	04MAR08				
RELEASE FORCE----- 1 OZ MIN			28 VOLTS DC RATING		115 VOLTS AC, 60 CPS	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			SIZE B TYPE I DRAWING NAME 91SX49 REV 3						
DIFFERENTIAL TRAVEL--- .005 MAX			SEA LEVEL		50,000 FT								SEA LEVEL		
OVERTRAVEL----- .004 MIN		INDUCTIVE	4 AMP	2.5 AMP	7 AMP										
		RESISTIVE	7 AMP	4 AMP	7 AMP										
		LAMP	2.5 AMP	2.5 AMP	2 AMP	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SCALE - WEIGHT:.003 LB MAX SHEET 1 OF 1						
		APPROVALS													

