





A

A



B

B



DETAIL C
SCALE 2:1

FCI

FCIconnect.com

ORDERING INFORMATION

D 0 9 S 1 3 A 6 R L 1 0 8 L F

SERIES
09
NO. OF CONTACTS
09
TYPE OF CONTACTS
S - SOCKET
TYPE OF TERMINATION
13-ANGLED SPILL
PITCH 2.54
FOOT PRINT-10.4
HEIGHT OF TERMINATION
A-2.10mm

LF - LEAD FREE
REVERSE SHELL ORIENTATION
TAPE&REEL PACKING

MOUNTING OPTIONS
RL ->LIF HARPOON+INSERT M3+METAL BRACKET
RX ->LIF HARPOON+INSERT UNC 4.40+METAL BRACKET
PLATING
4 - Gold Flash, 200 Mating/Un-mating performance
6 - 0.76 μ Gold, 500 Mating/Un-mating performance

"This product meets European Union Directives and other country regulations as described in GS-47-0004"

The housing will withstand exposure to 260°C peak temperature for 30 seconds in a convection, infra-red or vapor reflow oven solder application.

Packaging as per GS-14-920

TRUE POSITION : $\oplus \emptyset 0.36$

mat'l. code SEE.TECH.SPEC				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family DELTA-D
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
				angles	linear		REVERSE DELTA-D A/S FEMALE PIP CONNECTOR EUROPE VERSION
A	I10-0088	NG	2010/04/08				
B	I10-0249	NG	2010/12/29		.00±0.1		
C	ELX-I-19023	AB	2014/10/11	0°±1°	.000±.00X		
D	ELX-I-21007	AB	2015/06/03	dr	GEORGE V.JOSEPH 2005/12/19		
				engr	ALIAS.BABU 2014/10/11		
				chr	MITHUN.PAUL 2014/10/11		
				appd	BUJU.K.PAUL 2014/10/11		
sheet index		revision sheet	D 1				

FCI