


SHEET 1 OF 1





PCB MOUNTING




CIRCUIT: SPST









NOTES:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
   X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT RATING: 50mA @ 12VDC
5. TRAVEL: 0.30 ± 0.15mm
▲ 6. OPERATING FORCE: 160 ± 50gf
7. CONTACT RESISTANCE: 100mΩ MAX.
8. ELECTRICAL LIFE: 100,000 CYCLES
9. ▲ DENOTES CRITICAL PARAMETER
▲ 10. CONTACT MATERIAL: SILVER

REV	ECO NO	DESCRIPTION	DATE	BY
G	ECO-101515	print update	12/20/22	MW

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

OBJECT ID 000017203

TITLE TL1100FF160Q

SCALE	DATE	DR	DWG	REV
3:1	1/12/2011	BGL	P001101	G

Downloaded from Arrow.com.