

BA-2RV136-A2
PAGE 1 OF 1

M

DRAWING
NUMBER

9

ISSUE

REPLACES

RELEASE NO. SR-12753

CHECK

18 JAN 06

RJ

CHECK

26 JAN 67

LSD


CHECK

26 JAN 67

M B F

REVISIONS

A	SR-12753	RJR	27 FEB 67
B	0023200	SRH	9 FEB 70
C	0023559	SRH	9 FEB 70
D	0026699	SRH	9 FEB 70
E	00273287-J	JAL	22 NOV 91
F	00277390	SAD	9 JUN 94
G	00293346	DLT	26 AUG 98
H	00218387	TSG	18 JAN 06



NOTE

- ① - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- ② - CHARACTERISTICS MEASURED AT POINT A

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — — 8 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE — — — — 5 3/4 OZ MIN	L23 20A - 125, 250 OR 480 VAC 10A - 125 VAC "L"	UNLESS OTHERWISE NOTED
PRETRAVEL — — — — .400 MAX	1HP - 125 VAC, 2HP - 250 VAC	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL — — .070 MAX	1/2A - 125 VDC, 1/4A - 250 VDC	TOLERANCES ARE:
OVERTRAVEL — — — — .050 MIN	L288 L308 L315	ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
	CE 20(3)A 250V ~ T85 5E4	WEIGHT .065 LB