

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at
www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

Downloaded from Arrow.com.

May 2014

FDMS7608S

Dual N-Channel PowerTrench® MOSFET

Q1: 30 V, 22 A, 10.0 mΩ Q2: 30 V, 30 A, 6.3 mΩ

Features

Q1: N-Channel

- Max $r_{DS(on)}$ = 10.0 mΩ at V_{GS} = 10 V, I_D = 12 A
- Max $r_{DS(on)}$ = 13.6 mΩ at V_{GS} = 4.5 V, I_D = 10 A

Q2: N-Channel


- Max $r_{DS(on)}$ = 6.3 mΩ at V_{GS} = 10 V, I_D = 15 A
- Max $r_{DS(on)}$ = 7.2 mΩ at V_{GS} = 4.5 V, I_D = 13 A
- RoHS Compliant


General Description

This device includes two specialized N-Channel MOSFETs in a dual MLP package. The switch node has been internally connected to enable easy placement and routing of synchronous buck converters. The control MOSFET (Q1) and synchronous SyncFET™ (Q2) have been designed to provide optimal power efficiency.


Applications

- Computing
- Communications
- General Purpose Point of Load
- Notebook VCORE





Power 56



MOSFET Maximum Ratings T_A = 25°C unless otherwise noted

Symbol	Parameter		Q1	Q2	Units
V_{DS}	Drain to Source Voltage		30	30	V
V_{GS}	Gate to Source Voltage	(Note 3)	±20	±20	V
I_D	Drain Current -Continuous (Package limited)	T_C = 25 °C	22	30	A
	-Continuous	T_A = 25 °C	12[1a]	15[1b]	
	-Pulsed		50	60	
E_{AS}	Single Pulse Avalanche Energy	(Note 4)	29	33	mJ
P_D	Power Dissipation for Single Operation	T_A = 25°C	2.2[1a]	2.5[1b]	W
	Power Dissipation for Single Operation	T_A = 25°C	1.0[1c]	1.0[1d]	
T_J, T_{STG}	Operating and Storage Junction Temperature Range		-55 to +150		°C

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	57[1a]	50[1b]	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	125[1c]	120[1d]	
$R_{\theta JC}$	Thermal Resistance, Junction to Case	4.0	3.2	

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMS7608S	FDMS7608S	Power 56	13 ”	12 mm	3000 units

©2011 Fairchild Semiconductor Corporation

Downloaded from Arrow.com.

Electrical Characteristics T_J = 25°C unless otherwise noted


Symbol	Parameter	Test Conditions	Type	Min	Typ	Max	Units
Off Characteristics							
BV_{DSS}	Drain to Source Breakdown Voltage	I_D = 250 μA, V_{GS} = 0 V I_D = 1 mA, V_{GS} = 0 V	Q1 Q2	30 30			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μA, referenced to 25°C I_D = 10 mA, referenced to 25°C	Q1 Q2		13 19		mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = 24 V, V_{GS} = 0 V	Q1 Q2			1 500	μA
I_{GSS}	Gate to Source Leakage Current	V_{GS} = 20 V, V_{DS} = 0 V	Q1 Q2			100 100	nA nA
On Characteristics							
$V_{GS(th)}$	Gate to Source Threshold Voltage	V_{GS} = V_{DS}, I_D = 250 μA V_{GS} = V_{DS}, I_D = 1 mA	Q1 Q2	1.2 1.2	1.9 1.7	3.0 3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = 250 μA, referenced to 25°C I_D = 10 mA, referenced to 25°C	Q1 Q2		-6 -4		mV/°C
$r_{DS(on)}$	Static Drain to Source On Resistance	V_{GS} = 10 V, I_D = 12 A V_{GS} = 4.5 V, I_D = 10 A V_{GS} = 10 V, I_D = 12 A, T_J = 125°C	Q1		7.4 10.0 10.3	10.0 13.6 13.9	mΩ
		V_{GS} = 10 V, I_D = 15 A V_{GS} = 4.5 V, I_D = 13 A V_{GS} = 10 V, I_D = 15 A, T_J = 125°C	Q2		4.8 6.0 6.6	6.3 7.2 8.6	
g_{FS}	Forward Transconductance	V_{DD} = 5 V, I_D = 12 A V_{DD} = 5 V, I_D = 15 A	Q1 Q2		54 76		S
Dynamic Characteristics							
C_{iss}	Input Capacitance	Q1: V_{DS} = 15 V, V_{GS} = 0 V, f = 1 MHZ	Q1 Q2		1135 1380	1510 1835	pF
C_{oss}	Output Capacitance	Q2: V_{DS} = 15 V, V_{GS} = 0 V, f = 1 MHZ	Q1 Q2		390 478	520 635	pF
C_{rss}	Reverse Transfer Capacitance		Q1 Q2		42 60	65 90	pF
R_g	Gate Resistance		Q1 Q2	0.2 0.2	1.6 0.5	3.2 2.0	Ω
Switching Characteristics							
$t_{d(on)}$	Turn-On Delay Time	Q1 V_{DD} = 15 V, I_D = 12 A, R_{GEN} = 6 Ω	Q1 Q2		7 7	14 14	ns
t_r	Rise Time		Q1 Q2		3 3	10 10	ns
$t_{d(off)}$	Turn-Off Delay Time	Q2 V_{DD} = 15 V, I_D = 15 A, R_{GEN} = 6 Ω	Q1 Q2		19 20	35 36	ns
t_f	Fall Time		Q1 Q2		3 2	10 10	ns
$Q_{g(TOT)}$	Total Gate Charge	V_{GS} = 0V to 10 V; Q1 V_{DD} = 15 V, I_D = 12 A	Q1 Q2		18 21	24 30	nC
$Q_{g(TOT)}$	Total Gate Charge	V_{GS} = 0V to 5 V; Q1 V_{DD} = 15 V, I_D = 12 A	Q1 Q2		9 12	14 16	nC
Q_{gs}	Gate to Source Charge	Q2 V_{DD} = 15 V, I_D = 15 A	Q1 Q2		3.6 3.5		nC
Q_{gd}	Gate to Drain “Miller” Charge		Q1 Q2		2.5 3.0		nC

Downloaded from Arrow.com.

Electrical Characteristics T_J = 25°C unless otherwise noted

Symbol	Parameter	Test Conditions	Type	Min	Typ	Max	Units
Drain-Source Diode Characteristics							
V_{SD}	Source-Drain Diode Forward Voltage	V_{GS} = 0 V, I_S = 2 A (Note 2) V_{GS} = 0 V, I_S = 12 A (Note 2) V_{GS} = 0 V, I_S = 2 A (Note 2) V_{GS} = 0 V, I_S = 15 A (Note 2)	Q1 Q1 Q2 Q2		0.75 0.84 0.63 0.80	1.1 1.2 0.8 1.2	V
t_{rr}	Reverse Recovery Time	Q1 I_F = 12 A, di/dt = 100 A/μs	Q1 Q2		25 21	40 34	ns
Q_{rr}	Reverse Recovery Charge	Q2 I_F = 15 A, di/dt = 300 A/μs	Q1 Q2		9 19	18 33	nC

Notes:
1.$R_{\theta JA}$ is determined with the device mounted on a 1 in^2 pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.




a. 57 °C/W when mounted on a 1 in^2 pad of 2 oz copper



b. 50 °C/W when mounted on a 1 in^2 pad of 2 oz copper



c. 125 °C/W when mounted on a minimum pad of 2 oz copper



d. 120 °C/W when mounted on a minimum pad of 2 oz copper

2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.

3. As an N-ch device, the negative Vgs rating is for low duty cycle pulse occurrence only. No continuous rating is implied.

4. Q1: E_{AS} of 29 mJ is based on starting T_J = 25 °C; N-ch: L = 0.3 mH, I_{AS} = 14 A, V_{DD} = 27 V, V_{GS} = 10 V. 100% tested at L = 3 mH, I_{AS} = 3.75 A.

Q2: E_{AS} of 33 mJ is based on starting T_J = 25 °C; N-ch: L = 0.3 mH, I_{AS} = 15 A, V_{DD} = 27 V, V_{GS} = 10 V. 100% tested at L = 3 mH, I_{AS} = 3.9 A.

Downloaded from Arrow.com.

Typical Characteristics (Q1 N-Channel) T_J = 25°C unless otherwise noted




Figure 1. On Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Downloaded from Arrow.com.

Typical Characteristics (Q1 N-Channel) T_J = 25°C unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs Case Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

Downloaded from Arrow.com.

Typical Characteristics (Q1 N-Channel) T_J = 25°C unless otherwise noted




Figure 13. Junction-to-Ambient Transient Thermal Response Curve

Downloaded from Arrow.com.

Typical Characteristics (Q2 N-Channel) T_J = 25 °C unless otherwise noted




Figure 14. On-Region Characteristics




Figure 15. Normalized on-Resistance vs Drain Current and Gate Voltage




Figure 16. Normalized On-Resistance vs Junction Temperature




Figure 17. On-Resistance vs Gate to Source Voltage




Figure 18. Transfer Characteristics




Figure 19. Source to Drain Diode Forward Voltage vs Source Current

Downloaded from Arrow.com.

Typical Characteristics (Q2 N-Channel) T_J = 25°C unless otherwise noted




Figure 20. Gate Charge Characteristics




Figure 21. Capacitance vs Drain to Source Voltage




Figure 22. Unclamped Inductive Switching Capability




Figure 23. Maximum Continuous Drain Current vs Case Temperature




Figure 24. Forward Bias Safe Operating Area




Figure 25. Single Pulse Maximum Power Dissipation

Downloaded from Arrow.com.

Typical Characteristics (Q2 N-Channel) T_J = 25 °C unless otherwise noted




Figure 26. Junction-to-Ambient Transient Thermal Response Curve

Downloaded from Arrow.com.

Typical Characteristics (continued)

SyncFET™ Schottky body diode Characteristics

Fairchild's SyncFET™ process embeds a Schottky diode in parallel with PowerTrench® MOSFET. This diode exhibits similar characteristics to a discrete external Schottky diode in parallel with a MOSFET. Figure 27 shows the reverse recovery characteristic of the FDMS7608S.

Schottky barrier diodes exhibit significant leakage at high temperature and high reverse voltage. This will increase the power in the device.




Figure 27. FDMS7608S SyncFET™ Body Diode Reverse Recovery Characteristic







Figure 28. SyncFET™ Body Diode Reverse Leakage vs. Drain-Source Voltage


Downloaded from Arrow.com.








RECOMMENDED LAND PATTERN
(OPTION 1 - FUSED LEADS 5,6,7)



BOTTOM VIEW



RECOMMENDED LAND PATTERN
(OPTION 2 - ISOLATED LEADS)

NOTES:

A. PACKAGE DOES NOT FULLY CONFORM TO JEDEC STANDARD.

B. DIMENSIONS ARE IN MILLIMETERS.

C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 2009.

D. LAND PATTERN RECOMMENDATION IS EXISTING INDUSTRY LAND PATTERN.

E. DRAWING FILENAME: MKT-MLP08Prev2.

Downloaded from Arrow.com.

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Downloaded from Arrow.com.