

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 462A42X-X-01
Description : Slimline Transition, 4 Entry

NOTES

1. All dimensions are in

inches

millimeters
2. Dimensions appearing in table are as follows:

a - As Supplied

b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.




TABLE OF DIMENSIONS								
PART NUMBER	H		J,K & L		HO,JO,KO & LO ±15% b	W Nom b	P Nom b	R,S & T Nom b
	Min a	Max b	Min a	Max b				
462A423-X-01	2.37 [60,2]	.79 [20,1]	1.42 [36,1]	.79 [20,1]	1.09 [27,6]	.06 [1,5]	5.34 [135,6]	2.67 [67,8]
462A424-X-01	3.93 [99,8]	1.31 [33,3]	2.16 [54,9]	1.31 [33,3]	1.78 [45,2]	.07 [1,8]	8.16 [207,2]	4.08 [103,6]

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : K
Date : 6/9/99

Part Number : 462A42X-X-01
Description : Slimline Transition, 4 Entry

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 462A42X-X-01
Description : Slimline Transition, 4 Entry

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-50	Flexible, VPB	RT-1313			
-51	Flexible, EPB	RT-1321	/86,/164	S-1048, S-1124	Adhesive
-71	Flexible, Polyolefin	RT-1316	/42	S-1017	Adhesive

ORDERING INFORMATION

462A42X-X-01/XX

Base part number

Material dash number
(See Compatability Chart)

Modification number
(If necessary, see front of scd binder
for a complete list)

Adhesive slash number
(If necessary, see Compatability Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : K
Date : 6/9/99

Part Number : 462A42X-X-01
Description : Slimline Transition, 4 Entry