

Part Number : [2034382203](#)

Product Description : CP-6.5 Plug Housing, 6.50mm Pitch, Dual Row, 2 Circuits, Yellow, Glow-Wire Capable

Series Number : 203438

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[2034382203_sd.pdf](#)

[2034380001-PK-000.pdf](#)

[2034382203_stp.zip](#)


Specifications

[2034380001-PS-000.pdf](#)

[2034380001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	203438
Description	CP-6.5 Plug Housing, 6.50mm Pitch, Dual Row, 2 Circuits, Yellow, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	CP-6.5
UPC	191130083817

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	2
Color - Resin	Yellow
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.882/g
Number of Rows	2
Packaging Type	Bag

Panel Mount	No
Pitch - Mating Interface	6.50mm
Pitch - Termination Interface	6.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
CP-6.5 Receptacle Housing, Glow-Wire Capable, 6.50mm Pitch, Dual Row, 2 Circuits, Yellow	<u>1512072203</u>

Use with Part(s)

Description	Part Number
CP-6.5 Terminal Position Assurance (TPA) Retainer, 1 Circuit	<u>511430105</u>
CP-6.5 Wire-to-Wire Male Crimp Terminals	<u>205032</u>

This document was generated on Dec 26, 2025