



Circuit Board Indicators	Circuit Board Indicators - Through Hole Indicators	
Panel Mount Indicators	P/N# 5530113200F	3 mm Lens
Solid State Lighting		
Traffic Signals	Description	3 mm Bi-Level CBI
Vehicle Lighting	Package Options	50 Pieces Per Bag
Rail	Product Type	Through Hole Indicators
Obstruction Lighting	Sub Product Type	with Bi-Level Housing
Hazardous Area Lighting	Configuration	3 mm Lens
Heliport Lighting	Viewing	Right Angle
	Viewing Angle	60
	Test Current (mA)	10mA

Absolute Maximum Ratings (Ta = 25 °)	
Solder Temp	260Â° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2
Color	Red	Yellow
Lamp Type	Single Color	Single Color
LED Type	Standard Efficiency	Standard Efficiency
Intensity Min (mcd)	7.4	7.4
Intensity Typ (mcd)	10.0	10.0
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)	100	60
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.

5530113200F

[check stock](#)

how to purchase

[sales contacts](#)

[stock check](#)

[search](#)

[Product Line Search](#)

Please select a Product Line to search.

Circuit Board Indicators

[find](#)

[Part # / Text Search](#)

Part No.:

Text Search:

[search](#)

[quick links](#)

[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

[Application Notes](#)
[FAQs](#)

[Dialight Ltd \(UK\)](#)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)