
OMRON

Slide DIP Switch

A6H



Slide DIP Switches with Ultla-low profile and Half-pitch

- Industry's lowest-class profile of 1.55 mm.
- Half-pitch (1.27-mm) design reduces mounting space by 63%.
  (compared with conventional models)
- Washable, with seal tape available.
- Embossed taping available for small reel 100 pcs/ 500 pcs.





■List of Models

Tube Packaging

Type	Flat actuator			
	Standard		With seal tape	
Number of poles		Quantity per tube		Quantity per tube
2	**A6H-2101**	125	**A6H-2102**	125
4	**A6H-4101**	75	**A6H-4102**	75
6	**A6H-6101**	54	**A6H-6102**	54
8	**A6H-8101**	40	**A6H-8102**	40
10	**A6H-0101**	33	**A6H-0102**	33

Note: Order in multiples of the package quantity.

Embossed Taping

Type	Flat actuator											
	Standard						With seal tape					
												
Number of poles	Standard reel	Quantity per reel	Small reel	Quantity per reel	100 pcs reel	Quantity per reel	Standard reel	Quantity per reel	Small reel	Quantity per reel	100 pcs reel	Quantity per reel
2	**A6H-2101-P**	4,000	**A6H-2101-PM**	500	**A6H-2101-R100**	100	**A6H-2102-P**	4,000	**A6H-2102-PM**	500	**A6H-2102-R100**	100
4	**A6H-4101-P**		**A6H-4101-PM**		**A6H-4101-R100**		**A6H-4102-P**		**A6H-4102-PM**		**A6H-4102-R100**	
6	**A6H-6101-P**		**A6H-6101-PM**		**A6H-6101-R100**		**A6H-6102-P**		**A6H-6102-PM**		**A6H-6102-R100**	
8	**A6H-8101-P**		**A6H-8101-PM**		**A6H-8101-R100**		**A6H-8102-P**		**A6H-8102-PM**		**A6H-8102-R100**	
10	**A6H-0101-P**		**A6H-0101-PM**		**A6H-0101-R100**		**A6H-0102-P**		**A6H-0102-PM**		**A6H-0102-R100**	

Note: Order in multiples of the package quantity.

Downloaded from Arrow.com.

■Ratings/Characteristics


Rating (resistive load)		25 mA at 24 VDC 10 μA (minimum current) at 3.5 VDC
Ambient operating temperature		–20 to +70°C at 60% max. (with no icing or condensation)
Ambient operating humidity		35% to 95% (at +5 to +35°C)
Insulation resistance		100 MΩ min. (at 250 VDC with insulation tester)
Contact resistance (initial value)		200 mΩ max.
Dielectric strength	**Between terminals**	300 VAC for 1 min
Vibration resistance	**Malfunction**	10 to 55 Hz, 1.5-mm double amplitude
Shock resistance	**Malfunction**	300 m/s^2 min.
Durability	**Electrical**	1,000 operations min.
Washing		Standard models: Not possible, Models with seal tape: Possible
Degree of protection		IEC IP40
Operating force		0.29 to 4.9 N {30 to 500 gf}
Weight		0.06 g (2 poles) 0.09 g (4 poles) 0.12 g (6 poles) 0.15 g (8 poles) 0.18 g (10 poles)

■Dimensions (Unit: mm)

● **Flat Actuator**


Standard


A6H-□101
A6H-□101-P
A6H-□101-PM
A6H-□101-R100




With Seal Tape


A6H-□102
A6H-□102-P
A6H-□102-PM
A6H-□102-R100







Dimensions of PCB Pad (Reference)
(Top View)




No. of poles	Model		Dimension A
	Standard	With seal tape	
2	A6H-2101	A6H-2102	3.77
4	A6H-4101	A6H-4102	6.31
6	A6H-6101	A6H-6102	8.85
8	A6H-8101	A6H-8102	11.39
10	A6H-0101	A6H-0102	13.93

Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

■Internal Connection

Contact Form (Top View)



■Precautions

Be sure to read the Safety precautions common to all DIP Switches for correct use.

Downloaded from Arrow.com.

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact

Americas
https://components.omron.com/us

Europe
https://components.omron.com/eu

Asia-Pacific
https://components.omron.com/ap

China
https://components.omron.com.cn

Korea
https://components.omron.com/kr

Japan
https://components.omron.com/jp

© OMRON Corporation 2007-2022 All Rights Reserved.
In the interest of product improvement, specifications are subject to change without notice.

Cat. No. A117-E1-07
1122 (0207)

Downloaded from Arrow.com.