



+ RELAYS, CONTACTORS & SWITCHES

TO-5/.100 GRID



✓ Active

TE CONNECTIVITY (TE)
JMGSC-26LW = M39016/41-052L

1617149-4
TE Internal Number: 1617149-4
Mil-Spec: M39016/41-052L
Alias ID: JMGSC-26LW

Not EU RoHS Compliant
Not EU ELV Compliant

Contact Arrangement 2 Form C, DPDT, 2 C/O
Input Voltage (VDC) 14
Coil Suppression Diode Without
MOSFET Driver Without
Transistor Driver With

DOCUMENTATION

No documentation available.

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

MOSFET Driver Without
Product Type Relay
Relay Type Military/Aerospace High Performance
Coil Latching Without
Enclosure Type Hermetically Sealed

Configuration Features

Transistor Driver With

Electrical Characteristics

Input Voltage (VDC) 14
Coil Suppression Diode Without
Coil Voltage (VDC) 26.5
Coil Resistance (Ω) 3200
Coil Power Rating (DC) (mW) 219
Coil Polarity Protection Diode Without
Contact Switching Voltage (Max) 28
Actuating System DC
Coil Power Measurement Milliwatts
Shock 75G's, 6ms
Vibration 30G's, 10 – 3000Hz
Coil Magnetic System Non-Polarized, Monostable

Contact Features

Contact Arrangement 2 Form C, DPDT, 2 C/O
Contact Current Rating (A) 1
Contact Current Class Low Level – 1 A
Pin Configuration .175" Diameter Mounting Pad

Termination Features

Termination Type PC Pins

Mechanical Attachment

Mounting Type Printed Circuit Board

Usage Conditions

Operating Temperature Range ($^{\circ}\text{C}$) -65 – 125

Statement of Compliance

Statement of Compliance
PDF