
Part Number : 2218873322
Product Description : PowerWize 3.40mm, 2-circuit, Solder Tail, Mechanical Keying Option 2, Color Coded Natural, Right Angle Header, Tray
Series Number : 221887
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2218873322_sd.pdf

2218873321-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2215971000-AS-000.pdf

2215970001-PS-000.pdf

2215973000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	221887
Description	PowerWize 3.40mm, 2-circuit, Solder Tail, Mechanical Keying Option 2, Color Coded Natural, Right Angle Header, Tray
Application	Wire-to-Board
Component Type	PCB Header
Product Name	PowerWize
UPC	196823670947

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	65.0A
Voltage - Maximum	600V

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Diameter	3.40mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	14.420/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
Pitch - Mating Interface	11.00mm
Pitch - Termination Interface	11.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Pin-in-Paste SMT

Mates With / Use With

Mates with Part(s)

Description	Part Number
PowerWize 3.40mm, 2-circuit, Mechanical Keying Option 2, Color Coded Natural, Receptacle Housing, Bag	2215973002

Downloaded from Arrow.com.

Downloaded from Arrow.com.