






PRODUCT NUMBER	PITCH
V7xx71x100J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



SECTION P-P

Material:

- Item①Terminal body:Thermoplastic (UL94V-0)
- Item②Female contact:PhBz(CuSn), Tin plated
- Item③Terminal cover:Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

PART NO.: V7 xx 7 1 x 1 00J0 G

DIM		TOL				
		2P-5P	6P-10P	11P-15P	16P-20P	21P-24P
Dim L	N×5.0+2.0	±0.15	±0.20	±0.25	±0.30	±0.40
Dim B	(N-1)×5.0	±0.15	±0.20	±0.25	±0.30	±0.40
Dim C	N×5.0	0 -0.20		0 -0.30		
Dim D	(N-1)×5.0	±0.15	±0.20	±0.25	±0.30	±0.40

Solid block
No. of poles
02 2poles
03 3poles
...
24 24poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection		product family													
ltr				ecn no		dr		date		tolerances unless otherwise specified		 MM scale		TERMINAL BLOCK									
										angles				title									
										linear				TERMINAL BLOCK									
										X.±0.5				PLUGGABLE PCB PLUG,RIGHT ANGLE									
												X.X±0.3											
												X.XX±0.1											