



Part Number : [732520090](#)
Product Description : Precision Test Connector,
2.92mm PCB Jack Receptacle, 2-Hole Flange Mount,
Solderless Compression Contact, with 2 Screws
4.76mm, PCB Thickness 0.76-2.44mm, 50 Ohms
Series Number : 73252
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[732520090 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-89675-4400-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73252
Description	Precision Test Connector, 2.92mm PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, with 2 Screws 4.76mm, PCB Thickness 0.76-2.44mm, 50 Ohms
Application	RF
Comments	Solderless Compression
Product Name	Precision Test - 2.92mm
Style	PCB
Type	Subminiature
UPC	884982956018

Electrical

Frequency	40 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
------------------	-----

Gender	Jack
Keying to Mating Part	N/A
Net Weight	2.058/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount - Compression
PCB Thickness - Recommended	3.05mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Sep 22, 2025