



Representative Image

Catalog No. TY232MX

Description: CABLE TIE 18LB 8IN UV BLACK NYLON

UPC No 786210884172

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 203.2mm (8.0 Inches), Width of 2.3mm (0.09 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.09 in , 2.3 mm
Length	8 in , 202 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.06 to 2.01 in , 1.5 to 51 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	2.3 mm
Band width	0.09 inch
Length belt/tape/tie	202 mm
Length belt/tape/tie	8 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	51 mm
Max. bundle diameter	2.01 inch
Min. holding force	80 N
Operation temperature	-60-+105 °C
Operation temperature	-76-+221 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y