


1. MATERIALS AND FINISHES:
 - HD-BNC STR PLUG - BRASS, NICKEL PLATING
 - BNC STR PLUG - PHOSPHOR BRONZE, NICKEL PLATING
 - CABLE - BELDEN 4694R, BLACK
2. ELECTRICAL:
 - A. IMPEDANCE: 75 OHM
3. PACKAGING:
 - A. QUANTITY: SINGLE PACK
 - B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-850-218-XXX AND DATE CODE"

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	20-Nov-18	9701	SK



LENGTH TABLE			
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH IN INCHES [METERS] 'L'	LENGTH 'X' IN INCHES [METERS] MIN
95-850-218-006	-	6.00 [0.152]	0.75 [0.019]
-	95-850-218M025	9.84 [0.250]	
95-850-218-012	-	12.00 [0.305]	
95-850-218-018	-	18.00 [0.457]	
-	95-850-218M050	19.69 [0.500]	1.50 [0.038]
95-850-218-024	-	24.00 [0.610]	
-	95-850-218M075	29.53 [0.750]	
95-850-218-036	-	36.00 [0.914]	
-	95-850-218M100	39.37 [1.000]	
95-850-218-048	-	48.00 [1.219]	
-	95-850-218M125	49.21 [1.250]	
-	95-850-218M150	59.06 [1.500]	
95-850-218-060	-	60.00 [1.524]	
95-850-218-072	-	72.00 [1.829]	
-	95-850-218M200	78.74 [2.000]	
-	95-850-218M300	118.11 [3.000]	
95-850-218-120	-	120.00 [3.048]	
95-850-218-144	-	144.00 [3.658]	
95-850-218-180	-	180.00 [4.572]	
-	95-850-218M500	196.85 [5.000]	
95-850-218-300	-	300.00 [7.620]	
-	95-850-218M10L	393.70 [10.000]	
95-850-218L050	-	600.00 [15.240]	
-	95-850-218M20L	787.40 [20.000]	
95-850-218L075	-	900.00 [22.860]	
-	95-850-218M30L	1181.10 [30.000]	
95-850-218L100	-	1200.00 [30.480]	

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

☒ FREQUENCY: DC - 12 GHz	☒ CONTINUITY
☐ VSWR: ____ : 1 MAX	☒ HI-POT : 300 VRMS
☐ INS. LOSS : ____ dB MAX	☐ OTHER

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL SEE NOTES	DRAWN KAVI S	DATE 25-Sep-18	TITLE 75 OHM HD-BNC STR PLUG TO BNC STR PLUG USING BELDEN 4694R CABLE VARIOUS LENGTH		Amphenol RF www.amphenolrf.com
	ENGINEER KAVI S	DATE 25-Sep-18			
REFERENCE EAR # 8638	APPROVED K.CAPOZZI	DATE 20-Nov-18	SCALE: 1.5:1.0	SHEET 2 OF 2	DRAWING NO.95-850-218-XXX
CONFIGURATION LEVEL: In Work	CAD FILE		DWG SIZE B	REV A	ITEM NO.95-850-218-XXX
FINISH					PART NO.95-850-218-XXX