





NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
- NO CONTACT ON POS. A1
- METAL BRACKETS: ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- PCB-SNAPS: $\varnothing 3,1 \pm 0,1$ mm; PCB-THICKNESS: 1,6mm
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: [3011W1SCT99N40X CONEC ABC]

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)		
							material: SEE NOTES		
					date	name	title: D-SUB COMB. FEMALE 90° 11W1S with threaded insert, metal bracket and snap		
					drawn 14.08.09	Lehmenkühler			
					appd. 14.08.09	Koch			
					norm				
					d-old		dwg no: 13K1A2902 part no: 3011W1SCT99N40X		
	5 x b	Ä4224	10.02.2012	K.H.					DIN-A3
	a	Original		sh: 1					
	rev.	description	date	name					