




PC board drilling dimensions
(after plating – thickness: 1.60 to 3.20 mm)

Notes:

- 1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 5.60±0.15 mm.

mat'l code	surface	tolerance	projection	product family
ISO 1302	ISO 406	ISO 1001	MM	D-SUB
ecn no	dr	date	tolerances unless otherwise specified	title
F	EX-21256	AB	2015/07/14	MALE CONNECTOR DELTA-D LOW PROFILE
angles	linear	.0±0.1	.00±0.1	STRAIGHT – PRESS FIT
0±2°	dr	PESSON	1996/07/24	dwg no
engr	ALIAS BABU	2015/07/14	scale 2:1	sheet 1 of 1 size
chr	MITHUN PAUL	2015/07/14		C01 – 8646 – 0464
app	BIJU K PAUL	2015/07/14		A3
revision	F			Product Customer Drawing
sheet index	1			

LEAD FREE PART NUMBER

PART NUMBER	
200 Mating	D50P90C4P*00LF
500 Mating	D50P90C6P*00LF

Threaded ØT M3 = L
Threaded ØT 4.40 = X

GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C01-8646-0001