

Description

The ZTL431AQ, ZTL431BQ, ZTL432AQ, and ZTL432BQ are three terminal adjustable shunt regulators that offer excellent temperature stability and output current handling capability up to 100mA. The output voltage can be set to any chosen voltage between 2.5V and 20V by the selection of two external divider resistors.

The ZTL432AQ, ZTL432BQ has the same electrical specifications as the ZTL431AQ, ZTL431BQ but has a different pin out in SOT23 (F-suffix).

The ZTL431AQ, ZTL431BQ, ZTL432AQ, and ZTL432BQ are available in two grades with initial tolerances of 1% and 0.5% for the A and B grades respectively.

These devices are functionally equivalent to the TL431/TL432 except for maximum operation voltage, and they have an ambient temperature range of -40°C to +125°C as standard.

Features




- Temperature Range: -40°C to +125°C
- Reference Voltage Tolerance at +25°C
 - 0.5%: B Grade
 - 1%: A Grade
- 0.2Ω Typical Output Impedance
- Sink Current Capability: 1mA to 100mA
- Adjustable Output Voltage: V_{REF} to 20V
- Green Molding in SOT23 and SOT25
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **The ZTL431AQ, ZTL431BQ, ZTL432AQ and ZTL432BQ are suitable for automotive applications requiring specific change control and are AEC-Q100 qualified, have a grade 1 temperature rating, are PPAP capable, and are manufactured in IATF16949:2016 certified facilities.**

Applications


- Opto-Coupler Linearization
- Linear Regulators
- Improved Zener
- Variable Reference

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Pin Assignments



Typical Application



Absolute Maximum Ratings (Voltages specified are relative to the Anode pin unless otherwise stated.)

| Parameter | | Rating | Unit |
|---|----------------------|----------------------|--------------|
| Cathode Voltage (V_{KA}) | | 20 | V |
| Continuous Cathode Current (I_{KA}) | | 150 | mA |
| Reference Input Current Range (I_{REF}) | | -50 μ A to +10mA | — |
| Operating Junction Temperature | | -40 to +150 | $^{\circ}$ C |
| Storage Temperature | | -55 to +150 | $^{\circ}$ C |
| ESD Susceptibility | | | |
| HBM | Human Body Model | 2 | kV |
| MM | Machine Model | 200 | V |
| CDM | Charged Device Model | 1 | kV |

Caution: Stresses greater than the 'Absolute Maximum Ratings' specified above, can cause permanent damage to the device. These are stress ratings only; functional operation of the device at conditions between maximum recommended operating conditions and absolute maximum ratings is not implied. Device reliability can be affected by exposure to absolute maximum rating conditions for extended periods of time.

(Semiconductor devices are ESD sensitive and can be damaged by exposure to ESD events. Suitable ESD precautions should be taken when handling and transporting these devices.)

Package Thermal Data

| Package | θ_{JA} | P_{DIS} $T_A = +25^{\circ}\text{C}, T_J = +125^{\circ}\text{C}$ |
|---------|--------------------------|--|
| SOT23 | 380 $^{\circ}\text{C/W}$ | 260mW |
| SOT23F | 138 $^{\circ}\text{C/W}$ | 720mW |
| SOT25 | 250 $^{\circ}\text{C/W}$ | 400mW |


Recommended Operating Conditions (@ $T_A = +25^{\circ}\text{C}$, unless otherwise specified.)

| Symbol | Parameter | Min | Max | Unit |
|----------|-------------------------------------|-----------|------|--------------------|
| V_{KA} | Cathode Voltage | V_{REF} | 20 | V |
| I_{KA} | Cathode Current | 1 | 100 | mA |
| T_A | Operating Ambient Temperature Range | -40 | +125 | $^{\circ}\text{C}$ |


Electrical Characteristics (@ $T_A = +25^{\circ}\text{C}$, unless otherwise specified.)

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit |
|--|---|---|--|------|-------|---------------|
| V_{REF} | Reference Voltage | $V_{KA} = V_{REF}$ $I_{KA} = 10\text{mA}$ | A - grade 2.475 | 2.5 | 2.525 | V |
| | | | B - grade 2.487 | 2.5 | 2.513 | |
| V_{DEV} | Deviation of Reference Voltage Over Full Temperature Range | $V_{KA} = V_{REF}$ $I_{KA} = 10\text{mA}$ | $T_A = 0$ to $+70^{\circ}\text{C}$ — | 6 | 16 | mV |
| | | | $T_A = -40$ to $+85^{\circ}\text{C}$ — | 14 | 34 | |
| | | | $T_A = -40$ to $+125^{\circ}\text{C}$ — | 14 | 34 | |
| $\frac{\Delta V_{REF}}{\Delta V_{KA}}$ | Ratio of Change In Reference Voltage To the Change In Cathode Voltage | $I_{KA} = 10\text{mA}$ | $V_{KA} = V_{REF}$ to 10V — | -1.4 | -2.7 | mV/V |
| | | | $V_{KA} = 10\text{V}$ to 20V — | -1.0 | -2.0 | |
| I_{REF} | Reference Input Current | $I_{KA} = 10\text{mA}$, $R_1 = 10\text{k}\Omega$, $R_2 = \text{open}$ | — | 2 | 4 | μA |
| ΔI_{REF} | I_{REF} Deviation Over Full Temperature Range | $I_{KA} = 10\text{mA}$ $R_1 = 10\text{k}\Omega$ $R_2 = \text{open}$ | $T_A = 0$ to $+70^{\circ}\text{C}$ — | 0.8 | 1.2 | μA |
| | | | $T_A = -40$ to $+85^{\circ}\text{C}$ — | 0.8 | 2.5 | |
| | | | $T_A = -40$ to $+125^{\circ}\text{C}$ — | 0.8 | 2.5 | |
| $I_{KA(MIN)}$ | Minimum Cathode Current for Regulation | $V_{KA} = V_{REF}$ | — | 0.4 | 0.6 | mA |
| $I_{KA(OFF)}$ | Off State Current | $V_{KA} = 20\text{V}$, $V_{REF} = 0\text{V}$ | — | 0.1 | 0.5 | μA |
| R_Z | Dynamic Output Impedance | $V_{KA} = V_{REF}$, $f = 0\text{Hz}$ | — | 0.2 | 0.5 | Ω |


Typical Characteristics



Reference Voltage vs. Temperature




Dynamic Impedance vs. Frequency




Power Dissipation Derating

Typical Characteristics (continued)




Gain vs. Frequency




$I_{KA} = 10\text{mA}$, $T_A = 25^\circ\text{C}$

Test Circuit for Open Loop Voltage Gain




Pulse Response




$T_A = 25^\circ\text{C}$

Test Circuit for Pulse Response




Stability Boundary Condition




$V_{REF} < V_{KA} < 20\text{V}$, $I_{KA} = 10\text{mA}$, $T_A = +25^\circ\text{C}$

Test Circuit for Stability Boundary Conditions


Application Circuits




Shunt regulator




Higher current shunt regulator




Output control of a three terminal fixed regulator



Series regulator



Single supply comparator with temperature compensated threshold



Over voltage / under voltage protection circuit

DC Test Circuits




Figure 1. Test circuit for
 $V_{KA} = V_{REF}$




Figure 2. Test circuit for
 $V_{KA} > V_{REF}$




Figure 3. Test circuit for
off state current

Notes

Deviation of reference input voltage, V_{DEV} , is defined as the maximum variation of the reference input voltage over the full temperature range.

The average temperature coefficient of the reference input voltage, V_{REF} is defined as:

$$V_{REF}(\text{ppm}/^{\circ}\text{C}) = \frac{V_{DEV} \times 1,000,000}{V_{REF}(T1 - T2)}$$

The dynamic output impedance, R_Z , is defined as:


$$R_Z = \frac{\Delta V_Z}{\Delta I_Z}$$

When the device is programmed with two external resistors, $R1$ and $R2$, (Figure 2), the dynamic output impedance of the overall circuit, R'_Z , is defined as:


$$R'_Z = R_Z \left(1 + \frac{R1}{R2} \right)$$

Stability Boundary

The ZTL431AQ, ZTL431BQ, ZTL432AQ, and ZTL432BQ are stable with a range of capacitive loads. A zone of instability exists as demonstrated in the typical characteristic graph on page 4. The graph shows typical conditions. To ensure reliable stability, a capacitor of 4.7nF or greater is recommended between anode and cathode.



Ordering Information (Note 5)




| Tol. | Ordering Code | Package Code | Packaging (Note 4) | Part Mark | Reel Size | Tape Width (mm) | Quantity per Reel | Qualification | Status |
|------|---------------|--------------|--------------------|-----------|-----------|-----------------|-------------------|----------------------|--------------|
| 1% | ZTL431AQE5TA | E5 | SOT25 | 31A | 7", 180mm | 8 | 3,000 | Automotive Compliant | Active |
| | ZTL431AQFFTA | FF | SOT23F | 1V1 | 7", 180mm | 8 | 3,000 | Automotive Compliant | EOL (Note 6) |
| | ZTL431AQFTA | F | SOT23 | 31A | 7", 180mm | 8 | 3,000 | Automotive Compliant | Active |
| | ZTL432AQFFTA | FF | SOT23F | 1V2 | 7", 180mm | 8 | 3,000 | Automotive Compliant | EOL (Note 6) |
| | ZTL432AQFTA | F | SOT23 | 32A | 7", 180mm | 8 | 3,000 | Automotive Compliant | Active |
| 0.5% | ZTL431BQE5TA | E5 | SOT25 | 31B | 7", 180mm | 8 | 3,000 | Automotive Compliant | Active |
| | ZTL431BQFFTA | FF | SOT23F | 1V3 | 7", 180mm | 8 | 3,000 | Automotive Compliant | EOL (Note 6) |
| | ZTL431BQFTA | F | SOT23 | 31B | 7", 180mm | 8 | 3,000 | Automotive Compliant | Active |
| | ZTL432BQFFTA | FF | SOT23F | 1V4 | 7", 180mm | 8 | 3,000 | Automotive Compliant | EOL (Note 6) |
| | ZTL432BQFTA | F | SOT23 | 32B | 7", 180mm | 8 | 3,000 | Automotive Compliant | Active |

Notes: 4. Pad layout as shown in Diodes Incorporated's package outline PDFs, which can be found on our website at <http://www.diodes.com/package-outlines.html>.
5. See ZTL431/ZTL432 datasheet for commercial qualified versions.
6. ZTL431AQFFTA, ZTL431BQFFTA, ZTL432AQFFTA and ZTL432BQFFTA were made End-of-Life (EOL) PCN-2365 (<https://www.diodes.com/assets/PCN-Files/Diodes-PCN-2365-Rev1-EOL-Automotive.pdf>) with effect date 4 April, 2019.


Marking Information

(1) SOT23 and SOT23F (EOL – See Note 6)



| Orderable | Identification Code |
|--------------------|---------------------|
| ZTL431AQFFTA (EOL) | 1V1 |
| ZTL431AQFTA | 31A |
| ZTL432AQFFTA (EOL) | 1V2 |
| ZTL432AQFTA | 32A |
| ZTL431BQFFTA (EOL) | 1V3 |
| ZTL431BQFTA | 31B |
| ZTL432BQFFTA (EOL) | 1V4 |
| ZTL432BQFTA | 32B |

(2) SOT25




| Orderable | Identification Code |
|--------------|---------------------|
| ZTL431AQE5TA | 31A |
| ZTL431BQE5TA | 31B |

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(1) Package Type: SOT23



| SOT23 | | | |
|----------------------|-------|-------|-------|
| Dim | Min | Max | Typ |
| A | 0.37 | 0.51 | 0.40 |
| B | 1.20 | 1.40 | 1.30 |
| C | 2.30 | 2.50 | 2.40 |
| D | 0.89 | 1.03 | 0.915 |
| F | 0.45 | 0.60 | 0.535 |
| G | 1.78 | 2.05 | 1.83 |
| H | 2.80 | 3.00 | 2.90 |
| J | 0.013 | 0.10 | 0.05 |
| K | 0.890 | 1.00 | 0.975 |
| K1 | 0.903 | 1.10 | 1.025 |
| L | 0.45 | 0.61 | 0.55 |
| L1 | 0.25 | 0.55 | 0.40 |
| M | 0.085 | 0.150 | 0.110 |
| a | 0° | 8° | -- |
| All Dimensions in mm | | | |

(2) Package Type: SOT23F (EOL – See Note 6)

(3) Package Type: SOT25




| SOT25 | | | |
|----------------------|-------|------|------|
| Dim | Min | Max | Typ |
| A | 0.35 | 0.50 | 0.38 |
| B | 1.50 | 1.70 | 1.60 |
| C | 2.70 | 3.00 | 2.80 |
| D | - | - | 0.95 |
| H | 2.90 | 3.10 | 3.00 |
| J | 0.013 | 0.10 | 0.05 |
| K | 1.00 | 1.30 | 1.10 |
| L | 0.35 | 0.55 | 0.40 |
| M | 0.10 | 0.20 | 0.15 |
| N | 0.70 | 0.80 | 0.75 |
| α | 0° | 8° | - |
| All Dimensions in mm | | | |

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(1) Package Type: SOT23



| Dimensions | Value (in mm) |
|------------|---------------|
| C | 2.0 |
| X | 0.8 |
| X1 | 1.35 |
| Y | 0.9 |
| Y1 | 2.9 |

(2) Package Type: SOT23F (EOL – See Note 6)

(3) Package Type: SOT25



| Dimensions | Value |
|------------|-------|
| Z | 3.20 |
| G | 1.60 |
| X | 0.55 |
| Y | 0.80 |
| C1 | 2.40 |
| C2 | 0.95 |

Revision History

| Date | Revision | Changes | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|------------------|-----------------------|--|--|-----------------------|--------------------------------------|--------------------------------------|--------------|--------------|------------------|--------------|--------------|-----|-----|---------------|-----|-----|--------------|-----|----------------------|------|------|---|---------|-----------|-----------------------|-----------------------|---------------|--|--|-------|---------|-------|-------|--------|---------|--|-------|-------|---------|-------|-------|
| August 2014 | 1-2 | <p>Initial release</p> <p>Added further clarification of Automotive Grade and reference to Diodes Incorporated's definition (Pages 1 and 7)</p> <p>Amended generic part numbers from ZTL431Q/ZTL432Q to ZTL431xQ/ZTL432xQ (All pages Header)</p> <p>Addition of SOT23F variants: Pinout (page 1) Thermal impedance (Pages 2 and 3) Ordering information (page 7)</p> <table><tr><th>Tol.</th><th>Ordering Code</th></tr><tr><td rowspan="2">1%</td><td>ZTL431AQFFTA</td></tr><tr><td>ZTL432AQFFTA</td></tr><tr><td rowspan="2">0.5%</td><td>ZTL431BQFFTA</td></tr><tr><td>ZTL432BQFFTA</td></tr></table> <p>Package dimensions (page 8) and landing pad info (page 9)</p> | Tol. | Ordering Code | 1% | ZTL431AQFFTA | ZTL432AQFFTA | 0.5% | ZTL431BQFFTA | ZTL432BQFFTA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Tol. | Ordering Code | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1% | ZTL431AQFFTA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | ZTL432AQFFTA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0.5% | ZTL431BQFFTA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | ZTL432BQFFTA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| July 2016 | 2-2 | <p>Correction of ESD ratings (Note 7) (Page 2):</p> <table><tr><th colspan="2">ESD Rating</th><th>Incorrect revision 1-2 specification</th><th>Corrected revision 2-2 specification</th><th>Unit</th></tr><tr><td>HBM</td><td>Human Body Model</td><td>4000</td><td>2000</td><td>V</td></tr><tr><td>MM</td><td>Machine Model</td><td>400</td><td>200</td><td>V</td></tr><tr><td>CDM</td><td>Charged Device Model</td><td>1000</td><td>1000</td><td>V</td></tr></table> <p>Note 7 The actual physical ESD withstand capability is unaltered.</p> <p>Amendment of Recommended Maximum Power Dissipation based on revised maximum junction temperature of 125°C (Pages 2 and 3):</p> <table><tr><th rowspan="2">Package</th><th>Unchanged</th><th>Rev 1-2 specification</th><th>Rev 2-2 specification</th></tr><tr><th>θ_{JA}</th><th>P_{DIS} $T_A = +25^{\circ}C, T_J = +150^{\circ}C$</th><th>$P_{DIS}$ $T_A = +25^{\circ}C, T_J = +125^{\circ}C$</th></tr><tr><td>SOT23</td><td>380°C/W</td><td>330mW</td><td>260mW</td></tr><tr><td>SOT23F</td><td>138°C/W</td><td></td><td>720mW</td></tr><tr><td>SOT25</td><td>250°C/W</td><td>500mW</td><td>400mW</td></tr></table> | ESD Rating | | Incorrect revision 1-2 specification | Corrected revision 2-2 specification | Unit | HBM | Human Body Model | 4000 | 2000 | V | MM | Machine Model | 400 | 200 | V | CDM | Charged Device Model | 1000 | 1000 | V | Package | Unchanged | Rev 1-2 specification | Rev 2-2 specification | θ_{JA} | P_{DIS} $T_A = +25^{\circ}C, T_J = +150^{\circ}C$ | P_{DIS} $T_A = +25^{\circ}C, T_J = +125^{\circ}C$ | SOT23 | 380°C/W | 330mW | 260mW | SOT23F | 138°C/W | | 720mW | SOT25 | 250°C/W | 500mW | 400mW |
| ESD Rating | | Incorrect revision 1-2 specification | Corrected revision 2-2 specification | Unit | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| HBM | Human Body Model | 4000 | 2000 | V | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| MM | Machine Model | 400 | 200 | V | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| CDM | Charged Device Model | 1000 | 1000 | V | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Package | Unchanged | Rev 1-2 specification | Rev 2-2 specification | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | θ_{JA} | P_{DIS} $T_A = +25^{\circ}C, T_J = +150^{\circ}C$ | P_{DIS} $T_A = +25^{\circ}C, T_J = +125^{\circ}C$ | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| SOT23 | 380°C/W | 330mW | 260mW | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| SOT23F | 138°C/W | | 720mW | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| SOT25 | 250°C/W | 500mW | 400mW | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| December 2016 | 3-2 | <p>Now referring to Automotive Compliant instead of Automotive Grade throughout datasheet.</p> <p>Correction of SOT23F variants part marks (page 7)</p> <table><tr><th rowspan="2">SOT23F Orderable</th><th>Rev 2-2 specification</th><th>Rev 3-2 specification</th></tr><tr><th colspan="2">Part Mark</th></tr><tr><td>ZTL431AQFFTA</td><td>31A</td><td>1V1</td></tr><tr><td>ZTL432AQFFTA</td><td>32A</td><td>1V2</td></tr><tr><td>ZTL431BQFFTA</td><td>31B</td><td>1V3</td></tr><tr><td>ZTL432BQFFTA</td><td>32B</td><td>1V4</td></tr></table> <p>Amendment of pin number within datasheet (pages 1 and 7).</p> | SOT23F Orderable | Rev 2-2 specification | Rev 3-2 specification | Part Mark | | ZTL431AQFFTA | 31A | 1V1 | ZTL432AQFFTA | 32A | 1V2 | ZTL431BQFFTA | 31B | 1V3 | ZTL432BQFFTA | 32B | 1V4 | | | | | | | | | | | | | | | | | | | | | | |
| SOT23F Orderable | Rev 2-2 specification | Rev 3-2 specification | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | Part Mark | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ZTL431AQFFTA | 31A | 1V1 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ZTL432AQFFTA | 32A | 1V2 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ZTL431BQFFTA | 31B | 1V3 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ZTL432BQFFTA | 32B | 1V4 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| November 2018 | 4-2 | <p>Announcement of the End of Life (EOL) (PCN-2365) of the following devices:</p> <p>ZTL431AQFFTA ZTL432AQFFTA ZTL431BQFFTA ZTL432BQFFTA</p> | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| July 2019 | 5-2 | <p>Completion of the End of Life (EOL) (PCN-2365) of the following devices:</p> <ul style="list-style-type: none">• ZTL431AQFFTA• ZTL432AQFFTA• ZTL431BQFFTA• ZTL432BQFFTA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com