



**Part Number :** [430300002](#)

**Product Description :** Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel

**Series Number :** 43030

**Status :** Active

**Product Category :** Crimp Terminals

**Packaging Alternative :** [430300008](#) (Bag)



---

## Documents and Resources

### Drawings

[430300002 sd.pdf](#)

[PK-43030-001-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[430450001-AS-000.pdf](#)

[430450001-PS-KO-000.pdf](#)

[430450001-PS-SP-000.pdf](#)

[PS-43045-001.pdf](#)

[430450005-TS-000.pdf](#)

[430450006-TS-000.pdf](#)

[430450007-TS-000.pdf](#)


[TS-43045-001-001.pdf](#)

[TS-43045-002-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	 per SJ/T 11365-2006

EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	43030
Description	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Fit 3.0
UPC	800753683662

### Electrical

Current - Maximum per Contact	7.0A
-------------------------------	------

## Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	97.000/mg
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size (AWG)	20, 22, 24
Wire Size mm <sup>2</sup>	N/A

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Receptacle Housings	<u>43025</u>
Micro-Fit 3.0 Single Row Receptacle Housings	<u>43645</u>
Micro-Fit BMI Dual Row Receptacle Housings	<u>44133</u>
Micro-Fit BMI Single Row Receptacle Housings	<u>46623</u>
Micro-Fit TPA Single Row Receptacle Housings	<u>171850</u>
Micro-Fit TPA Receptacle Housings	<u>172952</u>

---

## Application Tooling

## Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>11030043</u>
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 30-20 AWG	<u>638120800</u>
PremiumGrade Hand Crimp Tool for Micro-Fit 3.0 Terminals, 30-20 AWG	<u>638190000</u>
FineAdjust Applicator for Insulation OD 1.30-1.85mm, 24-20 AWG Wire	<u>639004500</u>
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 24-20 AWG	<u>639018800</u>
FineAdjust Applicator for Micro-Fit 3.0 Terminals, for 24-20 AWG Wire with Insulation Diameter 0.91-1.09mm	<u>639018900</u>
T2 Terminator for Insulation OD 1.30-1.85mm, 24-20 AWG	<u>639104500</u>
T2 Terminator for Insulation OD 1.10-1.30mm - 24-20 AWG	<u>639118800</u>
T2 Terminator for Insulation OD 0.91-1.09mm - 24-20 AWG	<u>639118900</u>
FA2 Mechanical Feed Crimp Applicator for Micro-Fit 3.0 Male and Female Terminals, Double 24+24 AWG, UL 1061 Wires	<u>2130698700</u>
FA2 Mechanical Feed Crimp Applicator for Micro-Fit 3.0 Male and Female Terminals, Double 26+26 AWG, UL 1061 Wires	<u>2130698800</u>

## Japan

Description	Part Number
S-1 Applicator for Micro-Fit 3.0 Plug and Receptacle Crimp	<u>572983700</u>

Terminals, 24-20 AWG	
----------------------	--

---

This document was generated on May 19, 2026