
This browser does not have Java enabled.

1058628-1 Product Details



1058628-1

TE Internal Number: 1058628-1

Active

View 3D PDF

N Series RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector - RF
- Jack
- Coaxial Cable Termination Type = Solder/Clamp
- Applies To Cable
- Coaxial Cable Type (RG/U or Mfg.) = 402 Semi-Rigid/3.58 [.141]

View all Features

Quick Links
- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information

Product Drawings:
- OSN HIGH FREQ. BULKHEAD FEEDTHRU CABLE JACK SOLDER C... (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- 18.0 GHz OSN Bulkhead Feedthrough Cable Jack Solder ... (PDF, English)

CAD Files: (CAD Format & Compression Information)
- 2D Drawing (DXF, Version A)
- 3D Model (IGES, Version A)
- 3D Model (STEP, Version A)

List all Documents

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Connector - RF
- Gender = Jack
- Wire/Cable Type = Coaxial Cable
- Grade = Commercial
- Lightning/EMP Protection = None
- Dielectric Material = TFE Fluorocarbon
- Weatherproof = No

Mechanical Attachment:
- Panel Mount Retention = With
- Panel Mount Retention Type = Bulkhead
- Panel Attachment Style = Rear Mount

Electrical Characteristics:
- Frequency = DC - 18 GHz
- Connector Impedance (Ω) = 50
- Insulation Resistance (MΩ) = 5,000

Termination Features:
- Coaxial Cable Termination Type = Solder/Clamp

Dimensions:
- Panel Thickness (mm [in]) = 6.35 [0.250]

Body Features:
- Body Style = Straight
- Body Plating = Passivated
- Body Material = Stainless Steel
- Gasket Material = Silicone Rubber

Contact Features:
- Captured Center Contact = Without
- Center Contact Plating = Gold over Copper
- Center Contact Material = Beryllium Copper

Configuration Features:
- Coaxial Cable Type (RG/U or Mfg.) = 402 Semi-Rigid/3.58 [.141]

Industry Standards:
- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
- Applies To = Cable

Other:
- Brand = AMP
- Comment = High frequency.

© 2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved

Downloaded from Arrow.com.