Part Number : 2043160001
Product Description : Sentrality 8.00mm Top-entry, Knurled Press-fit Socket Assembly, Tray
Series Number : 204316
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2043160001_sd.pdf

2043180001-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2043130001-AS-000.pdf

2043130001-PS-000.pdf

2043130008-TS-000.pdf

2043131234-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	204316
Description	Sentrality 8.00mm Top-entry, Knurled Press-fit Socket Assembly, Tray
Application	Busbar-to-Board, Busbar-to-Busbar
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Name	Sentrality
UPC	191128468701

Agency

UL	E29179

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	8.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Gender	Female
Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	4.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Mounting Style	Through Hole
Net Weight	8.240/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Pins	203263
Sentrality 3.40mm Right-Angle Pins	204314

Downloaded from Arrow.com.