Document No. : SXC12518-00

KYOCERA SAW Filter

– RF filter for SDARS –

Type Name : VF11-2332M5UBA1

Aug., 21, 2024

KYOCERA Corporation

Corporate Electronic Components Group

Electronic Devices Division


© 2024 KYOCERA Corporation all right reserved


Downloaded from Arrow.com.

Dimensions & Test Circuit of SAW Filter


Dimensions

(Top View)






(Bottom View)



Test Circuit




Each port
Port extension(Time) : 100ps
Port extension(Loss) : 0.165dB

Unit	:	mm
V	:	Identification mark
U1	:	Identification no.
●	:	Index mark of pin 1
XXXX	:	Production code

Pin allocation

Pin No.	Function
(1)	Input
(2)	GND
(3)	Output
(4)	Output
(5)	GND

Recommendable Land Pattern



Unit : mm
: Electrode
Substrate Material : FR4

© 2024 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.

Rating

Items		Rating	Unit	Note
Operating Temperature Range		-40 to +125	deg.C	
Storage Temperature Range		-40 to +125	deg.C	
Max Input Power In Band		+10	dBm	5,000Hours,Ta=50deg.C ,CW
DC Voltage		0	dBm	*1)
ESD Level	Human Body Model	100	Volt	Complied to JESD22-A114
Moisture Sensitivity Level		2a		Complied to J-STD-033B.1
Nominal Input Impedance		50	ohm	Unbalance
Nominal output Impedance		100	ohm	Balance
AEC-Q200		Grade1		Complied to AEC-Q200

*1) When DC voltage is applied, a blocking capacitor is required.

© 2024 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.


Characteristic table


Items	Frequency (MHz)			Unit	VF11-2332M5UBA1 Specification. Aug., 21, 2024			Note
					min.	typ.	max.	
Minimum Insertion Loss (α_{min})	2315	to	2350	dB	-	1.1	-	
Maximum Insertion Loss	2315	to	2350	dB	-	1.2	2.2	-20deg.C to +85deg.C
	2315	to	2350	dB	-	1.2	2.4	
Ripple	2315	to	2350	dB	-	0.1	1.6	
Input VSWR	2315	to	2350	-	-	1.4	2.0	
Output VSWR	2315	to	2350	-	-	1.4	2.0	
Common Mode Rejection Ratio	2315	to	2350	dB	20	25	-	-20deg.C to +85deg.C
	2315	to	2350	dB	18	25	-	
Group Delay Ripple	2315	to	2350	ns	-	3	15	
Attenuation (Relative to α_{min})	88	to	880	dB	50	53	-	The value is difference between Absolute Attenuation and Minimum Insertion Loss. (= Absolute Attenuation - α_{min})
	880	to	1710	dB	40	48	-	
	1710	to	1910	dB	40	46	-	
	1910	to	2090	dB	35	47	-	
	2090	to	2190	dB	35	46	-	
	2190	to	2250	dB	30	43	-	
	2250	to	2275	dB	15	31	-	
	2400	to	2425	dB	15	27	-	
	2425	to	2500	dB	30	34	-	
	2500	to	2600	dB	35	43	-	
	2600	to	2800	dB	40	49	-	
	2800	to	3000	dB	40	47	-	
	3000	to	4000	dB	30	42	-	
	4000	to	4800	dB	30	50	-	
	4800	to	6000	dB	25	51	-	
Temperature range for specification				deg.C	-40 to +105			
Impedance	Input Port			ohm	50			
	Output Port			ohm	100			
Size (Length x Width)				mm	1.1 x 0.9			
Size (Thickness)				mm	0.55 max			


© 2024 KYOCERA Corporation all right reserved


Downloaded from Arrow.com.


Typical Curve Data

















VF11-2332M5UBA1
Typical Curve Data

Specification
-40 to +105 deg.C

Specification
-20 to +85 deg.C

© 2024 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.

Notice

1. Characteristics described in this datasheet are for references specifications shall be based on written documents agreed by each party.

2. Contents in this datasheet are subject to change without notice. It is recommended to confirm the latest information at the time of usage. Also, this datasheet is revised once a year. We may not be able to accept requests based on old datasheets.

3. Products in this datasheet are intended to be used in general electronic equipment such as office equipment, audio and visual equipment, communication equipment, measurement instrument and home appliances. It is absolutely recommended to consult with our sales representatives in advance upon planning to use our products in applications which require extremely high quality and reliability such as aircraft and aerospace equipment, traffic systems, safety systems, power plant and medical equipment including life maintenance systems.

4. Even though we strive for improvements of quality and reliability of products, it is requested to design with enough safety margin in equipment or systems in order not to threaten human lives directly or damage human bodies or properties by an accidental result of products.

5. It is requested to design based on guaranteed specifications for such as maximum ratings, operating voltage and operating temperature. It is not the scope of our guarantee for unsatisfactory results due to misuse or inadequate usage of products in the datasheet.

6. Operation summaries and circuit examples in this datasheet are intended to explain typical operation and usage of the product. It is recommended to perform circuit and assembly design considering surrounding conditions upon using products in this datasheet.

7. Technical information described in this datasheet is meant to explain typical operations and applications of products, and it is not intended to guarantee or license intellectual properties or other industrial rights of the third party or Kyocera.

8. Trademarks, logos and brand names used in this datasheet are owned by Kyocera or the corresponding third party.

9. Certain products in this datasheet are subject to the Foreign Exchange and Foreign Trade Control Act of Japan, and require the license from Japanese Government upon exporting the restricted products and technical information under the law. Besides, it is requested not to use products and technical information in the datasheet for the development and/or manufacture of weapons of mass destruction or other conventional weapons, nor to provide them to any third party with the possibility of having such purposes.

10. It is prohibited to reprint and reproduce a part or whole of this datasheet without permission.

© 2024 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.