

SIGNAL RELAY


2 POLES - 2A HIGH ISOLATION WIDE CONTACT GAP

FTR-C2 Series

RoHS Compliant

■ FEATURES

- DPDT 2A
- Contact gap: More than 2.0mm
- Conforms to IEC60950 / EN60950 / UL1950 / CSA C22.2 No.950 Working voltage 250V
- Insulation:
Clearance 2.0mm (between open contacts, coil and contacts, contact sets)
Creepage 2.5mm (between open contacts, coil and contacts, contact sets)
- High reliability bifurcated contacts
- Power consumption 300mW
- Latching types available
- RoHS compliant
- Plastic sealed



■ APPLICATIONS

VoIP, modems, STB, interlock switches etc.

■ PART NUMBERS

[Example] FTR-C2 G A 005 G
 (a) (b) (c) (d) (e)

(a)	Relay type	FTR-C2 series
(b)	Contact configuration	C : Through hole type G : Surface mount type
(c)	Coil type	A : Standard type B : Latching type
(d)	Coil rated voltage	005 : 3....24VDC Please refer to coil rating table
(e)	Contact material	G : Gold plated silver palladium (stationary contact) Silver palladium (movable contact)

Remarks: Actual marking on relay would not carry code FTR and be as below:

Ordering code: FTR-C2CA012G Actual marking: C2CA012G

Note: FTR-C2 series available in tube packaging only.

■ SPECIFICATIONS

Item			Specifications		Remarks/Conditions
			Non-latching FTR-C2()A	Latching FTR-C2()B	
Contact Data	Configuration		2c (2 Form C)		
	Construction		Bifurcated		
	Material		Gold plated silver palladium (stationary contact) Silver palladium (movable contact)		
	Resistance (initial)		Max. 150mΩ		At 1A, 6VDC
	Contact rating		0.3A, 125VAC/1A, 30VDC		Resistive
	Max. switching voltage		250VAC/220VDC		
	Max. switching power		62.5VA/30W		
	Max. carrying current		2A		
	Min. switching load ^{*1}		0.01mA, 10mVDC		Reference
Coil	Rated power		300mW	150mW	
	Operate power		169mW	85mW	
	Pulse width		-	Min. 20ms	
	Operating temperature range		-40°C to +85°C		No frost
Time	Operate (at nominal voltage)		Max. 15ms		Without bounce
	Release (at nominal voltage)		Max. 15ms		Without bounce
Life	Mechanical		Min. 10 x 10 ⁶ operations		
	Electrical (resistive)		Min. 100 x 10 ³ operations at 0.3A, 125VAC/1A, 30VDC		
Insulation	Insulation resistance		Min. 1,000MΩ		At 500VDC
	Dielectric strength	Open contacts	1,500VAC (50/60Hz) 1min.		
		Adjacent contacts	1,500VAC (50/60Hz) 1min.		
		Contacts to coil	2,000VAC (50/60Hz) 1min.		
	Surge strength	Contacts to coil	2,500V, 2 x 10μs standard wave		
	Clearance	Open contacts	2.0mm		
		Adjacent contacts	2.0mm		
		Contacts to coil	2.0mm		
	Creepage	Open contacts	2.0mm		
		Adjacent contacts	2.0mm		
		Contacts to coil	2.5mm		
Other	Vibration resistance	Misoperation>1μs	10 to 55 to 10Hz single amplitude 1.65mm		Coil ON/OFF, 3 axis, total 6 cycles
		Endurance	10 to 55 to 10Hz single amplitude 2.5mm		Coil OFF, 3 axis, total 6 hours
	Shock resistance	Misoperation>1μs	Min. 300m/s ² (11±1ms)		Coil ON/OFF, 3 axis, total 36 operations
		Endurance	Min. 1,000m/s ² (6±1ms)		Coil OFF, 3 axis, total 18 operations
	Dimensions / Weight		9.85 x 20.05 x 11.4mm / Approximately 3.7g		
	Sealing		RT III (plastic sealed)		

*1: Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

■ COIL DATA

• Standard (non-latching) type

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance (Ω) $\pm 10\%$	Must Operate Voltage* (VDC)	Must Release Voltage* (VDC)	Nominal Coil Power (mW)
003	3	30	2.25	0.3	300
005	5	83.3	3.75	0.5	
012	12	480	9.0	1.2	
024	24	1,920	18.0	2.4	

• Latching type

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance (Ω) $\pm 10\%$	Set Voltage* (VDC)	Reset Voltage* (VDC)	Nominal Coil Power (mW)
003	3	60	+2.25	-2.25	150
005	5	167	+3.75	-3.75	
012	12	960	+9.0	-9.0	
024	24	3,840	+18.0	-18.0	

Note: All values in the table are valid for 20°C and zero contact current unless otherwise specified.

* Specified operate values are valid for pulse wave voltage.

■ SAFETY STANDARDS

Type	Compliance	Contact Rating
UL	Flammability: UL 94-V-0 (plastics)	0.3A, 125VAC (resistive) 1A, 30VDC 2A, 30VDC 0.3A, 110VDC
	UL 508 File No. E63615	
CSA	C22.2 No.14	
	File No. LR 40304	

Comply with Telcordia specifications and meet BSI, IEC 60950-1:2006

Marking only for UL, CSA


■ PART NUMBER LIST

Part Number	Contact configuration	Coil Type	Contact Material
FTR-C2CA()G	Through hole	Standard	Gold plated silver palladium (stationary contact) Silver palladium (movable contact)
FTR-C2CB()G		Latching	
FTR-C2GA()G	Surface mount	Standard	
FTR-C2GB()G		Latching	


■ DIMENSIONS

Through Hole Type


• Dimensions



• Schematics (BOTTOM VIEW)




• Recommended PCB layout (BOTTOM VIEW)




Surface Mount Type


• Dimensions



• Schematics (TOP VIEW)



• Recommended PCB layout (TOP VIEW)



(): Reference
Unit: mm


Notes:

- Dimensions of the terminals do not include thickness of pre-soldering.
- Dimensions do not include tolerances. Please ask specification in the case you need tolerances.
- Tolerance of PCB layout: ± 0.1 unless otherwise specified.
- +/- : Polarity to apply set voltage, (+)/(-) : Polarity to apply reset voltage
- Contacts show de-energized/reset position


■ CHARACTERISTIC DATA

(Characteristic data is not guaranteed value but measured values of samples from production line.)


Distribution of operate/release voltage




Distribution of operate time




Distribution of release time




Set/reset time characteristic




Pulse characteristic




Distribution of contact resistance (Make contacts)




Distribution of contact resistance (Break contacts)



Operate range (non-latching)




Operate range (latching)



■ CHARACTERISTIC DATA

(Characteristic data is not guaranteed value but measured values of samples from production line.)



CAUTIONS

- All values mentioned in this datasheet are provided under ideal conditions. Please perform the confirmation test before actual use.
- Reflow soldering is not available with through hole type.
- Do not use relays in the atmosphere with sulfide gas, chloride gas or nitric oxide. Contact resistance may increase.
- Do not use silicon or silicon-containing product or materials near relays. It may cause contact failure.

Notes for latching relays

- Latching relays are shipped in the state reset, but state may change due to shock during transportation or mounting. Before using the relays, it is advisable to bring the relays in necessary state (set or reset) and program a circuit sequence. Otherwise, it will or will not operate simultaneously with power activation.
- Please connect relay coils according to specified polarity.
- Do not apply voltage to both set coil and reset coil at a time.

GENERAL INFORMATION

1. RoHS Compliance

- All relays produced by FCL Components are compliant with RoHS directive 2011/65/EU, including commission delegated directive 2015/863.

2. Recommended lead free solder condition

Flow Solder Condition:

Pre-Heating: Maximum 120°C within 90 sec.

Soldering: Dip within 5 sec. at 255°C±5°C solder bath

Relay must be cooled by air immediately after soldering

Solder by Soldering Iron:

Soldering Iron: 30-60W


Temperature: Maximum 350-360°C

Duration: Maximum 3 sec.

Reflow Solder Condition:

(Applicable only for reflow capable type)

Recommended reflow soldering profile: IRS (infrared reflow soldering)



Important notes for reflow soldering

- Temperature shall be measured at PC board upper surface.
- Temperature at PC board upper surface may be changed depending on size of PC board, components mounted on the PC board and/or heating method. Please perform the confirmation test with actual PC board.
- This reflow condition is applicable only for reflow-capable relays. Do not reflow reflow-incapable relays.
- Recommended solder for assembly: Sn-3.0 Ag -0.5 Cu.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

- Moisture Sensitivity Level Standard is not applicable to electromechanical relays unless otherwise indicated.

4. Tin Whiskers

- Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in-house test.

Contact

Japan

FCL COMPONENTS LIMITED
Shinagawa Seaside Park Tower
12-4, Higashi-shinagawa 4-chome,
Tokyo 140 0002, Japan
Tel: +81-3-3450-1682
Email: fcl-contact@cs.fcl-components.com

North and South America

FCL COMPONENTS AMERICA, INC.
c/o Masuda, Funai, Eifert & Mitchell, Ltd.
203 N LaSalle Street Suite 170, Chicago, IL
60601-1265, USA
Tel: +1-408-745-4900
Email: contact@fcl-components.us

Europe

FCL COMPONENTS EUROPE B.V.
Siriusdreef 9
2132 WT Hoofddorp
The Netherlands
Tel: +31-23-556-0910
Email: info@fcl-components.eu

China

FCL COMPONENTS (SHANGHAI) CO.,LTD.
Unit 1105, Central Park - Jing An,
No.329 Heng Feng Road, Shanghai
200070, China
Tel: +86-21-3253 0998
Email: fcsh@fcl-components.com

Asia

FCL COMPONENTS HONG KONG CO.,
LIMITED
Unit 2313, Seapower Tower, Concordia
Plaza, No.1 Science Museum Road,
TST, Kowloon, Hong Kong
Tel: +852-2881-8495
Email: fcsl@fcl-components.com

Web: www.fcl-components.com/en/

© 2026 FCL Components Limited. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

FCL Components Products are intended for general use, including without limitation, in personal, household and office environments, in buildings and for ordinary use in the industry. FCL Components Products are not intended to be used in applications where extremely high safety is required ("High Safety Required Applications"), such as, but not limited to, applications in nuclear facilities, in aircraft automatic flight control, in air traffic control, in mass transit system control, in missile launch system, in weapon systems, in medical equipment for life support or any application involving a direct serious risk of physical injury or death.

Please do not use FCL Components Products without securing the sufficient safety and reliability required for the High Safety Required Applications.

In addition, FCL Components shall not be liable against the customer and/or any third party for any claims or damages arising in connection with the use of FCL Components Products in the High Safety Required Applications.

FCL Components warrants that its Products, if properly used and services, will conform to their specification and will be free from defects in material and workmanship for twelve months from delivery.

The implied warranties of merchantability and fitness for a particular purpose and all other warranties, representations and conditions, express or implied by statute, trade usage or otherwise, except as set forth in this warranty, are excluded and shall not apply to the Products delivered.

The contents, data and information in this datasheet are provided by FCL Components Limited as a service only to its user and only for general information purposes. The use of the contents, data and information provided in this datasheet is at the users' own risk.

FCL Components has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

FCL Components Limited and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Nor do FCL Components Limited and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. July 10, 2026.