



NOTE:

- 1.) ALL DIMENSIONS
APPLY BEFORE PLATING
- 2.) THDS SHALL BE TO GAUGE FIT AFTER
PLATING OR OTHER FINISH
- 3.) SURFACE SHALL BE SMOOTH, AND FREE OF TOOL MARKS
- 4.) BREAK ALL SHARP CORNERS AND REMOVE BURRS
- 5.) CONCENTRICITY TO CENTER AXIS TO BE .002

STANDOFF				
PART NO.	LENGTH "A" ±.005	DRILL DEPTH "B" MAX	TAP DEPTH "C" MIN. DIM	NO. THDS
8216	.250	.218	.133	5-6
8217	.375	.312	.250	8-9
8218	.500	.330	.250	10-11
8219	.625	.330	.250	10-11
8220	.750	.330	.250	10-11
8221	.875	.330	.250	10-11
8222	1.000	.330	.250	10-11
8223	1.125	.330	.250	10-11
8224	1.250	.330	.250	10-11
8225	1.375	.330	.250	10-11
8226	1.500	.330	.250	10-11
8227	1.625	.330	.250	10-11
8228	1.750	.330	.250	10-11
8229	2.000	.330	.250	10-11
8230	2.500	.330	.250	10-11
8231	3.000	.330	.250	10-11



MATERIAL: BRASS-ALLOY 360- 1/2 HARD			FINISH: NICKEL		ABBATRON Electronic Connectors and Hardware 632 Arch Street, Meadville, Pa. 16335		
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED			TITLE: 8216-8231 BRASS HEX MALE/FEMALE STANDOFF				
XXX	XXXX	XXXXX					
±.010	±.005	---					
FRACTIONS	ANGLES	SCALE					
±1/64	±1°	4X					
HEAT TREAT: ---			DRAWN: T. LORD	DATE: 01/7/03	SIZE	DRAWING NUMBER	ISSUE
PLOT SCALE: 1=1			CHECKED: T. LORD	DATE: 01/7/03	B	SD: 8216-8231	Q
			APPROVED: T.LORD	DATE: 01/7/03			