



Part Number : [2033661010](#)

Product Description : QSFP-DD-to-2 QSFP56 (zQSFP+) Passive Cable Assembly, 56 Gbps, 30 AWG, 1.0m Length

Series Number : 203366

Status : Active

Product Category : High-Speed I/O Cable Assemblies



Documents and Resources

Drawings

[2033661010 sd.pdf](#)

[2033661005-PK.pdf](#)

Specifications

[2033660001-000.pdf](#)

[2033661010-001.pdf](#)

[2033661010-002.pdf](#)

[2033661010-003.pdf](#)

[2033661010-004.pdf](#)


[2033661010-005.pdf](#)

[2033661010-006.pdf](#)

[2033661010-007.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	203366
Description	QSFP-DD-to-2 QSFP56 (zQSFP+) Passive Cable Assembly, 56 Gbps, 30 AWG, 1.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP-DD-to-2 QSFP56, QSFP-DD-to-2 zQSFP+
Product Name	QSFP-DD,zQSFP Plus,zQSFP+
Type	Pluggable
UPC	191128457187

Electrical

Data Rate	56.0 Gbps
Impedance	100Ω

Physical

Cable Bundling	Woven Braid
Cable Length	1.0m
Circuits (Loaded)	MSA
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Zinc Die Cast
Material - Plating Mating	Gold
Net Weight	266.200/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Temp-Flex Twinax
Wire Size (AWG)	30

This document was generated on Apr 15, 2026