




735222-2 Product Details

[Share](#) [Print](#) [Email](#)


735222-2

TE Internal Number: 735222-2

Active

[View 3D PDF](#)

Multiple Circuit Housings with Tabs & Receptacles

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Contact
- Contact Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.81 mm
- Wire Range = 1.00-2.50² [17-13] mm [AWG]
- Insulation Diameter = 3.00-4.29 [.118-.169] mm [in]

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [TERMINAL FASTIN-ON .250 REC. \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version U\)](#)
- [3D Model \(IGES, Version U\)](#)
- [3D Model \(STEP, Version U\)](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Receptacle Style](#) = Straight
- [Wire/Cable Type](#) = Regular Wire
- [Finish](#) = Tin
- [Insertion Force](#) = Normal
- [Insulation Support](#) = With
- FASTON = Yes

Termination Features:

- [Crimp Type](#) = F-Crimp

Dimensions:

- [Mating Area Interface Dimensions \(mm \[in\]\)](#) = 6.35 x 0.81 [.250 x .032]
- [Insulation Diameter \(mm \[in\]\)](#) = 3.00-4.29 [.118-.169]

Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 1.00-2.50² [17-13]
- [Material](#) = Brass

Contact Features:

- [Contact Type](#) = Receptacle

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Packaging Features:

- [Packaging Method](#) = Strip

Other:

- [Line](#) = FASTIN-FASTON .250
- [Brand](#) = AMP

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

