


2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL	'A' +/- .031	'B' +/- .031	LABELS PER ROW	STANDARD PKG. QTY.
N100X075CBT	GMC4	.750 [19.05]	.875 [22.22]	3	10000
N100X125CBT		1.250 [31.8]	1.375 [34.9]		5000
N100X150CBT		1.500 [38.10]	1.625 [41.28]		5000
N100X175CBT		1.750 [44.45]	1.875 [47.63]		10000

NOTE:
1. MILLIMETER ARE IN [].

TITLE N100X075CBT, N100X125CBT, N100X150CBT & N100X175CBT OPTIMUM THERMAL TRANSFER LABELS					
CUSTOMER DRAWING					
ITEM REVISION NAME I00472F0/04					
DATASET FILE NAME I00472F0_DC/04A C10295 CUST DWG					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .12 [3.04] .xxx ± .025 [.635] .xx ± .062 [1.57] ANGLES ±				MATERIAL: SEE TABLE	
 THIRD ANGLE PROJECTION				DRAWING NUMBER: C10295	
DRAWN BY RVU	DATE 10/1/04	CHK JADE	SCALE NTS	SHT 1 OF 1	SIZE A

04A	10/10/2025	RVU	CREV	MSAD	A. PN, N100X150CBT, 5000 WAS 2500.	GAECN07474
01	1/4/2022	RVU	DAPE	JADE	COMBINATED ALL PARTS AS N050X***CBT TO BOM. UPDATE DRAWING TEMPLATE. ADDED N100X125CBT TO BOM.	GAECN06099
00	10/1/04	RVU			DRAWING RELEASE.	0000
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2

1