Part Number : 1200680189
Product Description : M12 Signal, A-Coded, In-Line Splitter, 1 x 4 Poles Male (Straight) to 2 x 3 Poles Female (Straight), 18 AWG, Yellow TPE Cable, 0.60m (1.97') Length
Series Number : 120068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : 884A30K03M006



Documents and Resources

Drawings

1200680189_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	M12 Signal, A-Coded, In-Line Splitter, 1 x 4 Poles Male (Straight) to 2 x 3 Poles Female (Straight), 18 AWG, Yellow TPE Cable, 0.60m (1.97') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Splitter - In-line
UPC	78678882258

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Color - Cable Jacket	Yellow
Drop Connector	Micro-Change (M12)
Drop Gender	N/A
Keyway	Single
LED Indicator	None

Downloaded from Arrow.com.

Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	0.60m
Leg 2 Length	0.60m
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Net Weight	112.801/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-30° to +80°C

Downloaded from Arrow.com.