



LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISION PER ECO-08-005408	05MAR08	JDP	CWR

- ① HOUSING: NYLON, 94V-0 RATED, COLOR BLUE.
CONTACTS: PHOSPHOR BRONZE.
- ② CONTACTS: 0.00254 [.000100] MIN TIN OVER 0.00127 [.000050] MIN NICKEL.
- ③ DATUMS AND BASIC DIMENSIONS TO BE ESTABLISHED BY CUSTOMER.
- ④ CONTACTS: 0.00076 [.000030] MIN GOLD IN CONTACT AREA. 0.00254 [.000100] MIN TIN ON
SOLDER POST, ALL OVER 0.00127 [.000050] MIN NICKEL.



2	78.74	[3.100]	31	81.69	[3.216]	83.82	[3.300]	1.27	[.050]	32	5-1658548-8
4	78.74	[3.100]	31	81.69	[3.216]	83.82	[3.300]	1.27	[.050]	32	5-1658548-7
2	76.20	[3.000]	30	79.15	[3.116]	81.28	[3.200]	0.00	[.000]	31	5-1658548-6
4	76.20	[3.000]	30	79.15	[3.116]	81.28	[3.200]	0.00	[.000]	31	5-1658548-5
2	73.66	[2.900]	29	76.61	[3.016]	78.74	[3.100]	1.27	[.050]	30	5-1658548-4
4	73.66	[2.900]	29	76.61	[3.016]	78.74	[3.100]	1.27	[.050]	30	5-1658548-3
2	71.12	[2.800]	28	74.07	[2.916]	76.20	[3.000]	0.00	[.000]	29	5-1658548-2
4	71.12	[2.800]	28	74.07	[2.916]	76.20	[3.000]	0.00	[.000]	29	5-1658548-1
2	68.58	[2.700]	27	71.53	[2.816]	73.66	[2.900]	1.27	[.050]	28	5-1658548-0
4	68.58	[2.700]	27	71.53	[2.816]	73.66	[2.900]	1.27	[.050]	28	4-1658548-9
2	66.04	[2.600]	26	68.99	[2.716]	71.12	[2.800]	0.00	[.000]	27	4-1658548-8
4	66.04	[2.600]	26	68.99	[2.716]	71.12	[2.800]	0.00	[.000]	27	4-1658548-7
2	63.50	[2.500]	25	66.45	[2.616]	68.58	[2.700]	1.27	[.050]	26	4-1658548-6
4	63.50	[2.500]	25	66.45	[2.616]	68.58	[2.700]	1.27	[.050]	26	4-1658548-5
2	60.96	[2.400]	24	63.91	[2.516]	66.04	[2.600]	0.00	[.000]	25	4-1658548-4
4	60.96	[2.400]	24	63.91	[2.516]	66.04	[2.600]	0.00	[.000]	25	4-1658548-3
2	58.42	[2.300]	23	61.37	[2.416]	63.50	[2.500]	1.27	[.050]	24	4-1658548-2
4	58.42	[2.300]	23	61.37	[2.416]	63.50	[2.500]	1.27	[.050]	24	4-1658548-1
2	55.88	[2.200]	21	58.83	[2.316]	60.96	[2.400]	0.00	[.000]	23	4-1658548-0
4	55.88	[2.200]	21	58.83	[2.316]	60.96	[2.400]	0.00	[.000]	23	3-1658548-9
2	50.80	[2.000]	20	53.75	[2.116]	55.88	[2.200]	0.00	[.000]	21	3-1658548-8
4	50.80	[2.000]	20	53.75	[2.116]	55.88	[2.200]	0.00	[.000]	21	3-1658548-7
2	48.26	[1.900]	19	51.21	[2.016]	53.34	[2.100]	1.27	[.050]	20	3-1658548-6
4	48.26	[1.900]	19	51.21	[2.016]	53.34	[2.100]	1.27	[.050]	20	3-1658548-5
2	45.72	[1.800]	18	48.67	[1.916]	50.80	[2.000]	0.00	[.000]	19	3-1658548-4
4	45.72	[1.800]	18	48.67	[1.916]	50.80	[2.000]	0.00	[.000]	19	3-1658548-3
2	43.18	[1.700]	17	46.13	[1.816]	48.26	[1.900]	1.27	[.050]	18	3-1658548-2
4	43.18	[1.700]	17	46.13	[1.816]	48.26	[1.900]	1.27	[.050]	18	3-1658548-1
2	40.64	[1.600]	16	43.59	[1.716]	45.72	[1.800]	0.00	[.000]	17	3-1658548-0
4	40.64	[1.600]	16	43.59	[1.716]	45.72	[1.800]	0.00	[.000]	17	2-1658548-9
2	38.10	[1.500]	15	41.05	[1.616]	43.18	[1.700]	1.27	[.050]	16	2-1658548-8
4	38.10	[1.500]	15	41.05	[1.616]	43.18	[1.700]	1.27	[.050]	16	2-1658548-7
2	35.56	[1.400]	14	38.51	[1.516]	40.64	[1.600]	0.00	[.000]	15	2-1658548-6
4	35.56	[1.400]	14	38.51	[1.516]	40.64	[1.600]	0.00	[.000]	15	2-1658548-5
2	33.02	[1.300]	13	35.97	[1.416]	38.10	[1.500]	1.27	[.050]	14	2-1658548-4
4	33.02	[1.300]	13	35.97	[1.416]	38.10	[1.500]	1.27	[.050]	14	2-1658548-3
2	30.48	[1.200]	12	33.43	[1.316]	35.56	[1.400]	0.00	[.000]	13	2-1658548-2
4	30.48	[1.200]	12	33.43	[1.316]	35.56	[1.400]	0.00	[.000]	13	2-1658548-1
2	27.94	[1.100]	11	30.89	[1.216]	33.02	[1.300]	1.27	[.050]	12	2-1658548-0
4	27.94	[1.100]	11	30.89	[1.216]	33.02	[1.300]	1.27	[.050]	12	1-1658548-9
2	25.40	[1.000]	10	28.35	[1.116]	30.48	[1.200]	0.00	[.000]	11	1-1658548-8
4	25.40	[1.000]	10	28.35	[1.116]	30.48	[1.200]	0.00	[.000]	11	1-1658548-7
2	22.86	[0.900]	9	25.81	[1.016]	27.94	[1.100]	1.27	[.050]	10	1-1658548-6
4	22.86	[0.900]	9	25.81	[1.016]	27.94	[1.100]	1.27	[.050]	10	1-1658548-5
2	20.32	[0.800]	8	23.27	[0.916]	25.40	[1.000]	0.00	[.000]	9	1-1658548-4
4	20.32	[0.800]	8	23.27	[0.916]	25.40	[1.000]	0.00	[.000]	9	1-1658548-3
2	17.78	[0.700]	7	20.73	[0.816]	22.86	[0.900]	1.27	[.050]	8	1-1658548-2
4	17.78	[0.700]	7	20.73	[0.816]	22.86	[0.900]	1.27	[.050]	8	1-1658548-1
2	15.24	[0.600]	6	18.19	[0.716]	20.32	[0.800]	0.00	[.000]	7	1-1658548-0
4	15.24	[0.600]	6	18.19	[0.716]	20.32	[0.800]	0.00	[.000]	7	1658548-9
2	12.70	[0.500]	5	15.65	[0.616]	17.78	[0.700]	1.27	[.050]	6	1658548-8
4	12.70	[0.500]	5	15.65	[0.616]	17.78	[0.700]	1.27	[.050]	6	1658548-7
2	10.16	[0.400]	4	13.11	[0.516]	15.24	[0.600]	0.00	[.000]	5	1658548-6
4	10.16	[0.400]	4	13.11	[0.516]	15.24	[0.600]	0.00	[.000]	5	1658548-5
2	7.62	[0.300]	3	10.57	[0.416]	12.70	[0.500]	1.27	[.050]	4	1658548-4
4	7.62	[0.300]	3	10.57	[0.416]	12.70	[0.500]	1.27	[.050]	4	1658548-3
2	53.34	[2.100]	21	56.29	[2.216]	58.42	[2.300]	1.27	[.050]	22	1658548-2
4	53.34	[2.100]	21	56.29	[2.216]	58.42	[2.300]	1.27	[.050]	22	1658548-1
FINISH	Z		Y	X		W		V		NO OF POS	PART NUMBER

[illegible]