




+ CONNECTORS
RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
3006 7985 00

Standard Coax

1057178-1
TE Internal Number: 1057178-1
Alias ID: 3006-7985-00

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Connector Interface N Type

Connector Style Jack

Mated Outer Diameter (Approximate) 19.05 mm [.75 in]

Impedance (Ω) 50

Cable Type RG 405 Semi-Rigid

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

OSN FLANGE MOUNT CABLE JACK-DIRECT SOLDER ATTACHMENT

PDF (TIFF AVAILABLE)

English

Instruction Sheets

Instruction Sheet (U.S.)

OSN Straight Cable Jack Direct Solder Attachment 1057178-1 And 1057119-1

PDF

English

OSN Straight Cable Jack Direct Solder Attachment 1057178-1 And 1057119-1

TIF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface N Type
Connector Style Jack
Connector & Contact Terminates To Wire & Cable

Electrical Characteristics

Impedance (Ω) 50

Body Features

Cable Connector Orientation Straight
Body Material Stainless Steel
Body Plating Material Gold

Contact Features

Center Contact Plating Material Gold
Center Contact Material Beryllium Copper
RF Connector Contact Configuration Not Captivated

Termination Features

Termination Method to Wire & Cable Solder

Mechanical Attachment

Panel Mount Retention Type Square Flange
Panel Attachment Style Front Mount

Dimensions

Mated Outer Diameter (Approximate) 19.05 mm [.75 in]

Usage Conditions

Cable Type RG 405 Semi-Rigid

Packaging Features

Packaging Method Carton

Other

Dielectric Material TFE Fluorocarbon
Grade Commercial

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF