

CGA3E2C0G1H150J080AD

TDK Item Description : CGA3E2C0G1H150JT***B




Equivalent C1608C0G1H150J for Automotive

Application & Main Feature

Automotive Grade (Conductive Epoxy Application)

Series

CGA3(1608) [EIA CC0603]



Dimensions

L 1.60mm +/-0.15mm
W 0.80mm +/-0.15mm
T 0.80mm +/-0.15mm
B 0.20mm Min.
G 0.30mm Min.

Temperature Characteristic

C0G (-55 to 125 degC 0+/-30ppm/degC)

Rated Voltage

1H (50Vdc)

Capacitance

15pF

Capacitance Tolerance

J (+/-5%)

O Factor

700 Min.


Insulation Resistance

10Gohm Min.


AEC-Q200

Yes


|Z|, ESR vs. Freq. Characteristics




DC Bias Characteristic



Cap. vs. Freq. Characteristic



Temperature Characteristics



All specifications are subject to change without notice.

January 4, 2016