


Part Number : 736420000
Product Description : HDM Board-to-Board Backplane Header, Vertical, Press-Fit, Open End, 72 Circuits
Series Number : 73642
Status : Active
Product Category : Backplane Connectors

Documents and Resources

Drawings

736420000_sd.pdf

PK-70873-0818-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-73642-9998-001.pdf

PS-73670-9999-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	73642
Description	HDM Board-to-Board Backplane Header, Vertical, Press-Fit, Open End, 72 Circuits
Application	Backplane
Comments	Standard Press-Fit
Component Type	PCB Header
Product Name	HDM
UPC	800754345057

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Data Rate	1.0 Gbps
Real Signals (per 25mm)	75
Shielded	No
Voltage - Maximum	250V AC

Physical

Downloaded from Arrow.com.

Circuits (Loaded)	72
Circuits (maximum)	72
Color - Resin	Black, Natural
Durability (mating cycles max)	250
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	3.371/g
Number of Columns	12
Number of Pairs	Open Pin Field
Number of Rows	6
Orientation	Vertical
Packaging Type	Tube
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.50mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.051µm
Polarized to PCB	No
Stackable	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Downloaded from Arrow.com.

Mates with Part(s)

Description	Part Number
HDM Daughtercard Receptacles	73632
HDM Vertical Daughtercard Receptacles	73780

Application Tooling

Global

Description	Part Number
Extraction Tool	621001000

Downloaded from Arrow.com.